

Pipe connector for ball valve with external thread

- internal thread Rp to external thread G
- incl. gasket



Type Overview

Type	DN	Rp ["]	G ["]	B [mm]	Suitable for	Weight
ZR4510	10	3/8	3/4	24	R4.. / R5.. DN10	0.070 kg
ZR4515	15	1/2	1	27	R4.. / R5.. DN15	0.10 kg
ZR4520	20	3/4	1 1/4	31	R4.. / R5.. DN20	0.18 kg
ZR4525	25	1	1 1/2	35	R4.. / R5.. DN25	0.28 kg
ZR4532	32	1 1/4	2	40	R4.. / R5.. DN32	0.38 kg
ZR4540	40	1 1/2	2 1/4	42	R4.. / R5.. DN40	0.45 kg
ZR4550	50	2	2 3/4	44	R4.. / R5.. DN50	0.69 kg

Technical data

Materials Used Materials Nickel-plated brass

Safety notes



- This accessory has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied during installation.
- The accessory may not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

General notes

Delivery notes In the scope of delivery: union nut (G thread), insert (RP thread), gasket (IT)

Dimensions

Dimensional drawings

