

Close-Off Pressure Globe Valve Threaded Body



	Non-Spring Return		Spring Return			Electronic Fail-Safe	
	LV	SV	LF	NF	AFB	LVK	SVK
2-way							
G215B(S)-C	250		160			250	
G215B(S)-F	250		160			250	
G215B(S)-G	250		160			250	
G215B(S)-J	250		160			250	
G220B(S)-J	250		155			250	
G220B(S)-K	250		155			250	
G225B(S)-K	250		147			250	
G225B(S)-L	250		147			250	
G232B(S)-M	250		141			250	
G240B(S)-N	250			250	210	250	
G250B(S)-N	250			250	120	250	
3-way Mixing							
G315B-G		250		250			250
G315B-J		250		250			250
G320B-K		250		250			250
G325B-L		250		179			250
G332B-M		246		133			246
G340B-N		137			167		137
G350B-N		86			105		86
3-way Diverting							
G315B-G		250		166			250
G315B-J		250		166			250
G320B-K		182		101			182
G325B-L		109		60			109
G332B-M		82		44			82
G340B-N		46			56		46
G350B-N		29			35		29

Tech.Doc - 4/18 - Subject to change. © Belimo Aircontrols (USA), Inc.

	Non-Spring Return		Spring Return		Electronic Fail-Safe	
	EV	RV	AF	2*AF	AVK	2*GK
2-way Pressure Comp ANSI 125						
G665C	140		140		140	
G680C	140		140		140	
G6100C	140			140	140	
G6125C	140			140	140	
G6150C	140			110	140	
2-way Pressure Comp ANSI 125						
G665CS, G665LCS	125		125		125	
G680CS, G680LCS	125		125		125	
G6100CS, G6100LCS	125			125	125	
G6125CS, G6125LCS	125			125	125	
G6150C, G6150LCS	125			125	125	
2-way Pressure Comp ANSI 250						
G665C-250	310		232		310	
G680C-250	310		181	310	310	
G6100C-250	310			310	310	
G6125C-250	310			241	300	
G6150C-250	310			182	232	
2-way Pressure Comp ANSI 250						
G665CS-250, G665LCS-250	280		232		280	
G680CS-250, G680LCS-250	280		181		280	
G6100CS-250, G6100LCS-250	280				280	
G6125CS-250, G6125LCS-250	280				280	
G6150CS-250, G6150LCS-250	280				280	280
3-way ANSI 125 Mixing						
G765, G765S	106	125	31	70	84	125
G780, G780S	73	125	21	48	57	102
G7100, G7100S	40	75		26		56
G7125, G7125S		47				35
G7150, G7150S		32				24
3-way ANSI 250 Mixing						
G765-250, G765S-250	106	198	31	70	84	149
G780-250, G780S-250	73	136	21	48	57	102
G7100-250, G7100S-250	40	75		26		56
G7125-250, G7125S-250		47				
G7150-250, G7150S-250		32				
3-way ANSI 125/250 Diverting						
G765D, G765DS	140		140		140	
G780D, G780DS	140		140		140	
G7100D, G7100DS	140		140		140	
G7125D, G7125DS	140			140	140	
G7150D, G7150DS	140			140		
3-way ANSI 125/250 Diverting						
G765DS-250	310		310		310	
G780DS-250	310		310		310	
G100DS-250	310		310		310	
G7125DS-250	310			310		
G7150DS-250	310			310		

Tech.Doc - 4/18 - Subject to change. © Belimo Aircontrols (USA), Inc.