

# Actuator solutions for MP-Bus®.

## Water solutions



Types <sup>1)</sup>	Rating	Passive sensor	Active sensor	Switching contact	Parameterisable	UK24BAC	UK24MOD
<b>Actuators for control valves/open-close ball valves</b>							
CQ24A-MPL	1 Nm	-	-	-	-	■	■
LR24A-MP	5 Nm	■	■	■	■	■	■
NR24A-MP	10 Nm	■	■	■	■	■	■
SR24A-MP	20 Nm	■	■	■	■	■	■
<b>Actuators for control valves/open-close ball valves with fail-safe</b>							
CQK24A-MPL	1 Nm	■	-	■	■	■	■
TRF24-MFT	2 Nm	■	-	■	■	■	■
LRF24-MP	4 Nm	■	■	■	■	■	■
NRF24A-MP	10 Nm	■	■	■	■	■	■
<b>Actuators for globe valves</b>							
LV24A-MP-TPC	500 N	■	■	■	■	■	■
NV24A-MP-TPC	1000 N	■	■	■	■	■	■
SV24A-MP-TPC	1500 N	■	■	■	■	■	■
EV24A-MP-TPC	2500 N	■	■	■	■	■	■
<b>Actuators for globe valves with fail-safe</b>							
NVK24A-MP-TPC	1000 N	■	■	■	■	■	■
AVK24A-MP-TPC	2000 N	■	■	■	■	■	■
<b>Fast running actuators for globe valves</b>							
LVC24A-MP-TPC	500 N	■	■	■	■	■	■
NVC24A-MP-TPC	1000 N	■	■	■	■	■	■
SVC24A-MP-TPC	1500 N	■	■	■	■	■	■
<b>Fast running actuators for globe valves with fail-safe</b>							
NVKC24A-MP-TPC	1000 N	■	■	■	■	■	■
<b>Actuators for butterfly valves</b>							
SR24A-MP-5	20 Nm	■	■	■	■	■	■
GR24A-MP-5/7	40 Nm	■	■	■	■	■	■
JRCA-BAC-S2-T	90 Nm	■	■	■	■	■	■
PRCA-BAC-S2-T-200	160 Nm	■	■	■	■	■	■
PRCA-BAC-S2-T-250	160 Nm	■	■	■	■	■	■
PRCA-BAC-S2-T	160 Nm	■	■	■	■	■	■
PRKCA-BAC-S2-T-200	160 Nm	■	■	■	■	■	■
PRKCA-BAC-S2-T-250	160 Nm	■	■	■	■	■	■
PRKCA-BAC-S2-T	160 Nm	■	■	■	■	■	■
SY4-24-MP-T	400 Nm	■	■	■	■	■	■

<sup>1)</sup> The currently available product range can be found on your local Belimo website.

# Actuator solutions

## Modbus / BACnet combined.

### Water solutions



Types <sup>1)</sup>	Rating	Passive sensor	Active sensor	Switching contact	Parameterisable	Hybrid
<b>Actuators for butterfly valves</b>						
JRCA-BAC-S2-T	90 Nm	■	■	■	■	■
PRCA-BAC-S2-T-200	160 Nm	■	■	■	■	■
PRCA-BAC-S2-T-250	160 Nm	■	■	■	■	■
PRCA-BAC-S2-T	160 Nm	■	■	■	■	■
PRKCA-BAC-S2-T-200	160 Nm	■	■	■	■	■
PRKCA-BAC-S2-T-250	160 Nm	■	■	■	■	■
PRKCA-BAC-S2-T (with fail-safe)	160 Nm	■	■	■	■	■

### Safety solutions

Standard actuator for fire dampers	Rating	Passive sensor	Active sensor	Switching contact	Parameterisable	Hybrid
BKN230-24-MOD for connecting BF.(T)24(-T)-ST	4/9/11/18 Nm	–	–	–	■	–

### Room and system solutions

VAV-Compact rotary actuators	Rating	Passive sensor	Active sensor	Switching contact	Parameterisable	Hybrid
LMV-D3-MOD	5 Nm	–	■	■	■	■
NMV-D3-MOD	10 Nm	–	■	■	■	■
SMV-D3-MOD	10 Nm	–	■	■	■	■
<b>VAV-Compact linear actuator</b>						
LHV-D3-MOD	150 N	–	■	■	■	■
<b>VAV-Universal</b>						
VRU-D3-BAC	–	■	■	■	■	■
VRU-M1-BAC	–	■	■	■	■	■
VRU-M1R-BAC	–	■	■	■	■	■

<sup>1)</sup> The currently available product range can be found on your local Belimo website.