



DN	A	B
DN 350	M24	≤270 Nm
DN 400	M27	≤360 Nm
DN 450	M27	≤360 Nm
DN 500	M30	≤510 Nm
DN 600	M33	≤700 Nm
DN 700	M33	≤700 Nm



