

Current transducer, solid core, 0...10 amp sensing range, DC 0...5 V terminal strip sensor output.



Technical data

Operating Temperature	-30...140°F
Humidity Range	5...95% (non-condensing)
Max Sense Voltage	AC 600 V
Mounting / Installation	Removable mounting tab provided. The wire clamp locks against the wire being monitored, securing the unit in place.
Sensor Type	solid core with voltage output
Origin	made of US and non-US parts
Accuracy	96.8% full scale
Loading	1% error @ 180 kΩ
Sensing Range	0...10 amps
Sensor Output	DC 0...5 V (terminal strip, accepts #14-22 AWG wire)
Approvals	UL Listed, C-UL, CE, RoHS, UL916, UL864, California State Fire Marshall

Dimensions

