




5-year warranty



## Technical data


<b>Functional data</b>	Fluid Temp Range (water)	Please Refer to Manufacturer's Valve Specifications
<b>Mounting Position</b>		configuration specific (X10-X35)
<b>Applicable valve size</b>		2...2.5" [50...65]
<b>Materials</b>		
Hardware		zinc plated steel
Spindle		stainless steel
Frame, plate, base		stainless steel
Coupling		stainless steel
<b>Suitable actuators</b>		
Non-Spring		(2*GMB(X))
Spring		(2*AFB(X))
Electrical fail-safe		(2*GKB(X))

For close-off pressure reference Select Pro or retrofit technical documentation.

## Product features

<b>Default/Configuration</b>	The actuator is sold separately from the linkage. This allows users to select any actuator with the desired control signal. Since the linkage utilises standard airside actuators, they can be purchased at any time and mounted in the field.
<b>Application</b>	<p>The UFLK retrofit kit is designed to easily attach to the valve mounting pad on select 3-way competitor valves utilizing Belimo actuators.</p> <p>This kit will help to restore service without removal of the valve, saving down time. The UFLK retrofit kit is available in various configurations for use with both 2-way and 3-way valves utilizing single or dual actuation.</p>
<b>Operation</b>	The UFLK kit and mounted actuator(s) are capable of rotating 95° in both CW and CCW directions. This allows the disc to fully open or close. When directional needs vary, the actuators can be flipped or directional switch turned to a new rotation. Refer to the actuator wiring guides on Master/Slave wiring for dual mounted actuators.

## Dimensions



2\*GKB, 2\*GKX, 2\*GMB, 2\*GMX

A	B	C	D
7.0" [178]	9.0" [229]	9.0" [229]	20.0" [508]