




5-year warranty




Technical data

| | | |
|------------------------------|--|---|
| Functional data | Fluid Temp Range (water) | Please Refer to Manufacturer's Valve Specifications |
| Mounting Position | | configuration specific (X10-X35) |
| Applicable valve size | | 10" [250] |
| Materials | | |
| Hardware | | zinc plated steel |
| Spindle | | stainless steel |
| Frame, plate, base | | stainless steel |
| Coupling | | stainless steel |
| Suitable actuators | Non-Spring | SY4 |
| | For close-off pressure reference Select Pro or retrofit technical documentation. | |

Product features

| | |
|------------------------------|---|
| Default/Configuration | The actuator is sold separately from the linkage. This allows users to select the specified actuator with the desired control signal. Since the linkage utilises standard SY actuators, they can be purchased at any time and mounted in the field. |
| Application | The UFLK retrofit kit is designed to easily attach to the valve mounting pad on select competitor valves utilizing Belimo SY industrial series actuators. This kit will help to restore service without removal of the valve, saving down time. The UFLK retrofit kits are available in various configurations for use with both 2-way and 3-way valves where applicable. |
| Operation | The UFLK and mounted actuator(s) are capable of rotating 90° in both CW and CCW directions. This allows the disc to fully open or close. When directional needs vary, the actuator's directional switch can be flipped to change the rotation. The SY/PR is NEMA 4X rated and can be used outdoors. |

Dimensions



| A | B | C | D |
|-------------|-------------|-------------|-------------|
| 25.2" [640] | 13.3" [337] | 11.5" [292] | 10.0" [254] |