



22WDP-11../22WDP-51.. 0... 10 V	22WDP-13../22WDP-53.. 4... 20 mA
1 Uv: AC/DC 15...24 V / AC 24 V	Uv: DC 15...24 V
2 GND	GND Out 4...20 mA
3 Out 0...10 V	

