



22WP-11../22WP-51.. 0... 10 V	22WP-13../22WP-53.. 4... 20 mA
1 Uv: AC/DC 15...24 V/AC 24 V	Uv: DC 15... 24 V
2 GND	GND Out 4... 20 mA
3 Out 0... 10 V	

