

- Thermoelectric tripping device
- Manual reset


Thermoelectric Tripping Device BAE280 AP



Technical data

Electrical data	Rated voltage	AC/DC 24V AC 220V
	Rated current	1A
	Connection	Terminal strip
Functional data	Operating temperature thermal trips	Tf: duct temperature 280°C
	Manual reset	Manual reset button
Safety	Protection class	Grounded enclosure
	Degree of protection	IP44
	Testing note	BAE280 AP is an IP44 electronic temperature sensor, it is not recommended to repeat the test for the same sample in an oil bath
Dimensions / weight	Ambient temperature range	-30...+50°C
	Storage temperature	-40...+50°C
	Maintenance	Maintenance-free
	Dimensions (L x M x H)	See "Dimensions"
	Weight	Approx. 0.4kg

Wiring diagrams



Dimensions [mm]

