

# Piping Package Nomenclature

P 2	1 1 1	1 2 1 3	1 2 1 1	2
<b>Piping Package</b> P = Piping Package <b>Valve Type</b> 2 = 2-way CCV 3 = 3-way CCV E = ePIV / EV P = PIQCV Q = QCV Z = Zone <b>Options</b> S = Supply Side Package X = Extension Package	<b>Union</b> <b>Valve Size</b> 1 = ½" 2 = ¾" 3 = 1" 4 = 1...¾" 5 = ¾...½" A = 1½" B = 1¼" C = 2" D = 1¼...1" E = 1½...1¼" F = 2...1½" G = 1...½" H = 1¼...¾" J = 1½...1" K = 2...1¼" <b>Body End</b> 1 = Female NPT 2 = Copper Sweat <b>Configuration</b> 1 = Standard <b>Tailpiece End</b> Male NPT Only	<b>Isolation Valve / Manual Balance Valve</b> <b>Valve Size</b> 1 = ½" 2 = ¾" 3 = 1" 4 = 1...¾" 5 = ¾...½" A = 1½" B = 1¼" C = 2" D = 1¼...1" E = 1½...1¼" F = 2...1½" G = 1...½" H = 1¼...¾" J = 1½...1" K = 2...1¼" <b>Body End</b> 1 = Female NPT 2 = Copper Sweat <b>Configuration</b> 1 = Standard <b>Tailpiece End</b> Male NPT Only	<b>Strainer / Isolation Valve</b> <b>Valve Size</b> 1 = ½" 2 = ¾" 3 = 1" 4 = 1...¾" 5 = ¾...½" A = 1½" B = 1¼" C = 2" D = 1¼...1" E = 1½...1¼" F = 2...1½" G = 1...½" H = 1¼...¾" J = 1½...1" K = 2...1¼" <b>Body End</b> 1 = Female NPT 2 = Copper Sweat <b>Configuration</b> 1 = Standard <b>Tailpiece End (Strainer Option)</b> 1 = Female NPT 2 = Copper Sweat 3 = Male NPT <b>Tailpiece End (Isolation Valve Option)</b> 0 = Select "0" for Isolation Valve Option Male NPT Only	<b>Hose</b> <b>Diameter &amp; Length</b> 1 = ½" (12" length) 2 = ½" (24" length) 3 = ¾" (12" length) 4 = ¾" (24" length) 5 = 1" (12" length) 6 = 1" (24" length) 7 = ½" (18" length) 8 = ¾" (18" length) 9 = 1" (18" length) A = 1¼" (18" length) H = 1¼" (24" length) B = 1¼" (36" length) C = 1½" (18" length) D = 1½" (24" length) E = 1½" (36" length) F = 2" (24" length) G = 2" (36" length)

Please refer to typical Piping Package layouts on pages prior to ordering. Nomenclature chart does not include all options or press connection types. Manual Balance Valves require flow consideration for proper sizing. Download Select-Pro software for complete options and available configurations. Consult factory for lead time. Non-standard items have increased lead time.

Non-Standard items include:

- 1¼...2" packages of all types
- All sizes of Unions, Manual Balance Valves, Strainers and Isolation Valves without P/T ports
- All sizes of Unions, Manual Balance Valves, Strainers and Isolation Valves with extensions
- All sizes of components with press fit connections

**Note: Piping Package smart code does not include the Belimo control valve in the price.**