




EXT-AC-R..



| Type R = D (mm) | | | | | | | | | | |
|-----------------|-------|-------|-------|-------|-------|-------|-----|-----|------|------|
| 100 | 125 | 160 | 200 | 250 | 315 | 400 | 500 | 630 | 800 | 1000 |
| K-factor | | | | | | | | | | |
| 20.18 | 33.01 | 56.22 | 90.23 | 138.4 | 226.3 | 373.6 | 594 | 956 | 1559 | 2456 |

EXT-AC-L..



| | | Type L = W (mm) | | | | | | | | | | |
|--------|-------------|-----------------|------|------|------|------|------|------|------|------|------|------|
| | | 200 | 250 | 300 | 400 | 500 | 600 | 700 | 800 | 900 | 1000 | 1200 |
| H (mm) | Probe (qty) | K-factor | | | | | | | | | | |
| 100 | 1 | 50 | 62 | 75 | 99 | 124 | 149 | 174 | 199 | 224 | 249 | 298 |
| 150 | | 83 | 104 | 124 | 166 | 207 | 249 | 290 | 332 | 373 | 414 | 497 |
| 200 | | 116 | 145 | 174 | 232 | 290 | 348 | 406 | 464 | 522 | 580 | 696 |
| 250 | | 149 | 187 | 224 | 298 | 373 | 448 | 522 | 597 | 671 | 746 | 895 |
| 300 | | 182 | 228 | 274 | 365 | 456 | 547 | 638 | 729 | 821 | 912 | 1094 |
| 350 | 2 | 199 | 249 | 298 | 398 | 497 | 597 | 696 | 796 | 895 | 995 | 1194 |
| 400 | | 232 | 290 | 348 | 464 | 580 | 696 | 812 | 928 | 1044 | 1160 | 1393 |
| 450 | | 265 | 332 | 398 | 530 | 663 | 796 | 928 | 1061 | 1194 | 1326 | 1591 |
| 500 | | 298 | 373 | 448 | 597 | 746 | 895 | 1044 | 1194 | 1343 | 1492 | 1790 |
| 600 | | 365 | 456 | 547 | 729 | 912 | 1094 | 1277 | 1459 | 1641 | 1824 | 2188 |
| 700 | 3 | 414 | 518 | 622 | 829 | 1036 | 1243 | 1451 | 1658 | 1865 | 2072 | 2487 |
| 800 | | 481 | 601 | 721 | 962 | 1202 | 1442 | 1683 | 1923 | 2163 | 2404 | 2885 |
| 900 | | 547 | 684 | 821 | 1094 | 1368 | 1641 | 1915 | 2188 | 2462 | 2735 | 3282 |
| 1000 | 4 | 597 | 746 | 895 | 1194 | 1492 | 1790 | 2089 | 2387 | 2686 | 2984 | 3581 |
| 1100 | | 663 | 829 | 995 | 1326 | 1658 | 1989 | 2321 | 2652 | 2984 | 3316 | 3979 |
| 1200 | | 729 | 912 | 1094 | 1459 | 1824 | 2188 | 2553 | 2918 | 3282 | 3647 | 4377 |
| 1300 | 5 | 779 | 974 | 1169 | 1558 | 1948 | 2337 | 2727 | 3117 | 3506 | 3896 | 4675 |
| 1400 | | 845 | 1057 | 1268 | 1691 | 2114 | 2536 | 2959 | 3382 | 3805 | 4227 | 5073 |
| 1500 | | 912 | 1140 | 1368 | 1824 | 2279 | 2735 | 3191 | 3647 | 4103 | 4559 | 5471 |