

**Differential Pressure Switch**

For monitoring overpressure, vacuum and differential pressure of air or other non-combustible, non-aggressive gases for both HVAC and energy management applications. Automatic reset and field adjustable setpoints and switching hysteresis.


**Technical Data**

<b>Electrical Data</b>	Electrical connection	terminals for wire 0.5...1.5 mm <sup>2</sup>
	Cable entry	Cable gland with strain relief Ø6...8 mm (1/2" NPT conduit adapter included)
<b>Functional Data</b>	Output signal switch note	contact current max. 1.0 A (0.4) / AC 250 V
	Application	air
<b>Measuring Data</b>	Measuring values	differential pressure
	Measuring fluid	air, non-combustible and non-aggressive gases
<b>Materials</b>	Housing	base: PA 6.6 cover: ps
<b>Safety Data</b>	Ambient humidity	max. 95% r.H., non-condensing
	Ambient temperature	-5...140°F [-20...60°C]
	Fluid temperature	-5...140°F [-20...60°C]
	Storage temperature	-40...185°F [-40...85°C]
	EU Conformity	CE Marking
	Certification IEC/EN	IEC/EN 60730-1
	Certification UL	ETL listed, UL508, CSA C22.2 No.14
	Degree of protection IEC/EN	IP54
	Degree of protection NEMA/UL	NEMA 13
Quality Standard	ISO 9001	

**Safety Notes**


This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application. Unauthorised modifications are prohibited. The product must not be used in relation with any equipment that in case of a failure may threaten humans, animals or assets.

Ensure all power is disconnected before installing. Do not connect to live/operating equipment.

Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied during installation.

The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

**Remarks**

**Recommended installation positions** The specifications for the switching pressure refer to a vertical installation position, which is also recommended with downward pressure connections. For horizontal mounting position with upwards directed AMP connecting lugs, the switching values are approx. 20 Pa higher.

It is not permitted to mount the pressure switch upside down!


Scope of delivery

PVC tube 2 m  
 2 x Duct connectors (plastic)  
 Screws  
 1/2" NPT conduit adapter

Accessories

Optional accessories	Description	Type
	Duct connector kit for 01APS-..., Multipack 50 pcs.	A-22AP-A05.1

Wiring Diagram



Dimensions

Dimensions

