




2-year warranty



**Technical data**

|                           |                                |  |
|---------------------------|--------------------------------|--|
| <b>Functional data</b>    | Valve Size                     | 0.5" [15]                              |
|                           | Fluid                          | chilled or hot water, up to 50% glycol |
|                           | Fluid Temp Range (water)       | 32...212°F [0...100°C]                 |
|                           | Body Pressure Rating           | 300 psi                                |
|                           | Close-off pressure $\Delta$ ps | 30 psi                                 |
|                           | Flow characteristic            | on/off                                 |
|                           | Flow Pattern                   | 2-way                                  |
|                           | Leakage rate                   | ANSI Class III 0.1%                    |
|                           | Cv                             | 3.5                                    |
|                           | Body pressure rating note      | 300 psi                                |
| <b>Materials</b>          | Valve body                     | forged brass                           |
|                           | Housing seal                   | EPDM                                   |
|                           | Seat                           | EPDM                                   |
|                           | Pipe connection                | sweat                                  |
| <b>Suitable actuators</b> | Spring                         | ZONE                                   |

**Product features**

**Application** This valve is typically used on fan coil units, baseboards or other hydronic applications where fail safe operation on 2-wire control is required. This valve is suitable for use in a hydronic system with variable or constant flow.

This valve is designed to fit in compact areas where on/off or control is required using 24 VAC or 120 VAC.

**Dimensions**
**Dimensional drawings**


| A          | B         | C         | D          | E         | F         |
|------------|-----------|-----------|------------|-----------|-----------|
| 4.0" [102] | 2.8" [70] | 3.5" [89] | 4.3" [110] | 1.2" [30] | 1.2" [31] |