



High-Low Mounting Kit

Remote Enclosure for Dual Gas Monitors

Belimo gas monitors can sense up to two different gases on the same device. The high low mounting kit (A-22G-A14) is a remote enclosure that allows one gas monitor to sense two gases at various installation heights of up to 7 feet (2 meters) apart.



Discover the advantages
www.belimo.com

BELIMO
®

Typical Applications

Boiler Mechanical Rooms: A carbon monoxide (CO) gas monitor is installed at 3-7 feet (1-2 meters) from the floor, and a natural gas monitor (CH4) is mounted at 1-3 feet (0.3-1 meters) from the ceiling.

Parking Garages/Automobile Parkades: Mount carbon monoxide monitors at 3-7 feet (1-2 meters) from the floor and a nitrogen dioxide monitor at 50% of the ceiling height when gasoline and diesel vehicles are expected.

Loading Docks and Truck Maintenance: Install a carbon monoxide monitor at 3-7 feet (1-2 meters) from the floor and a propane monitor at 1-2 feet (0.3-0.6 meters) from the floor.

The high low mounting kit consists of an enclosure to remotely monitor a gas, an interface connector to plug into an existing gas monitor, and a 7 foot (2 meter) plug in data cable (type RJ45) that interconnects the two.


Please note: The provided prefabricated interconnection cable allows for quick installation. The use of alternative cables or cables over 7 feet are not supported using Belimo gas monitors.



Interface Connector



Data Cable



Dual Gas Monitor



Enclosure