




EXT-KA-SQ100

用户手册



EXT-KA-SQ100 空气质量监测仪是电气装置。请在使用前阅读安全须知，并采取必要预防措施来降低火灾、电击或受伤的风险。

安全须知

- 为了避免危险，必须始终由制造商、服务代理商或有资质的人员进行安装、维护等操作。
- 安装与维护前，请确保电源已断开。
- 请勿以任何方式改造或使用非官方配件维修、维护设备。
- 请勿将设备置于高湿度环境或可能直接接触水的位置，比如厨房、浴室或洗衣房等。
- 请勿将设备置于室外。
- 请勿将设备放在散热器、壁炉、烤箱、炉灶等热源附近。
- 请勿在使用中覆盖设备。



产品规格

输入电压：100-240V 交流
输入频率：50Hz
输入功率：10W
存储温度：0-55°C
尺寸：90*90*50mm
重量：300g
建议温度范围：0-50°C
建议湿度范围：5-95% 相对湿度（无凝结）


 www.belimo.com

 info.asiapacific@belimo.ch



EXT-KA-SQ100

User Manual



EXT-KA-SQ100 is an electrical appliance. Please read the safety warnings before use and take the necessary precautions to reduce the risk of fire, electric shock, or injury.

Safety Warnings

- To reduce safety risks, always use service personnel from the manufacturer or service provider, or other qualified personnel for installation and maintenance.
- Make sure the power is OFF during installation or maintenance.
- DO NOT tamper with or use nonofficial spare parts for repair or maintenance.
- DO NOT use the device in environments with high humidity or possible direct exposure to water, such as kitchens, bathrooms, laundry rooms, etc.
- DO NOT use the device in an outdoor environment.
- DO NOT use the device near heat sources, such as radiators, furnaces, ovens, or stoves.
- DO NOT cover the device during use.



Specifications

Input Voltage: 100-240V AC
Input Frequency: 50Hz
Input Power: 10W
Storage Temperature: 0-55°C
Dimensions: 90*90*50mm
Weight: 300g
Operation Temperature: 0-50°C
Operation Humidity: 5-95% relative humidity (non-condensing)

 www.belimo.com

 info.asiapacific@belimo.ch