



u

Nominal voltage	AC/DC 24V
Nominal voltage frequency	50/60Hz
Nominal voltage range	AC 19.2...28.8V / DC 19.2...28.8V
Power consumption DC	0.2W
Power consumption AC	0.2VA
Nominal resistance	100k
Linearity	Max. 1%
Connection supply / control	Terminals 1.5 mm ² Cu wire or 1.0 mm ² Cu strands (Cable diameter 5...9.5 mm, 4-wire)
Controller signal	0...20 mA → 0...10 V
Output load	On the 4...20 mA-Output: 0...600 (wire resistance + controller input resistance)
Protection class IEC/EN	III, Safety Extra-Low Voltage (SELV)
Degree of protection IEC/EN	IP66
EMC	CE according to 2014/30/EU
Mode of operation	Type 1
Rated impulse voltage supply	0.8 kV
Pollution degree	3
Ambient temperature	-30...50°C
Storage temperature	-40...80°C
Ambient humidity	Max. 95% RH, non-condensing
Servicing	maintenance-free
Weight	0.11 kg
Housing cover	Black
Housing base	Black

o



Supply and control are not electrically isolated from one another.

The device must not be used outside the specified field of application, especially not in aircraft or in any other airborne means of transport.

Outdoor applications: only possible if no (sea) water, snow, ice, solar radiation and aggressive gases act directly on the device, and it is guaranteed that the ambient conditions are always within the limit values according to the data sheet.

Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied during installation.


The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

Electrical installation



For restrictions with respect to maximum signal cable length, see actuator data sheets

Wiring diagrams



Dimensions

Dimensional drawings
(Unit: mm)

