

Powerful and versatile: The new GM actuator



User-friendly maintenance LED device status indication

The LED indicator enables quick status checks of all devices on-site. Its clear signals – off, on, or blinking – simplify troubleshooting and reduce training needs.

Fast and safe wiring without tools Innovative electrical interfaces

Our tool-free lever mechanism allows fast wiring and one-step device connection; the detachable terminal block streamlines installation for speed and efficiency.

Each wire connects effortlessly with small levers, eliminating the need for screws and tools.



Save energy Smooth and energy-efficient operation with the M600


The M600 microchip enhances motor control, ensuring low noise operation and efficient energy management. This results in significantly lower overall energy consumption.

3-point control type Holding torque = nominal torque

The GM actuator now supports 3-point control, ensuring precise torque and reliable positioning – even during holding phases.

Easy device replacement Innovative electrical interfaces

Replacing a device is simple and efficient, with no need for rewiring. Just unplug the old device, replace it, replug, and reapply the parameters, with an easy-to-use process.



Simple setup

Guided configuration with Belimo Assistant 2

With NFC and the Belimo Assistant 2 app, devices can be read even without power. This feature provides useful information in multiple languages, making it easy to verify proper operation. Connect your Belimo devices, check or modify settings, and display identification data.

