

Ball Valve (VS), 1/2", 2-way, Cv 4



2-year warranty

Type overview

| Type | DN |
|------------|----|
| B2050VS-04 | 15 |

Technical data

| | | |
|--------------------|-----------------------------------|---|
| Functional data | Valve size [mm] | 0.5" [15] |
| | Fluid | chilled or hot water, up to 60% glycol, steam |
| | Fluid Temp Range (water) | -30...138°C [-22...280°F] |
| | Body Pressure Rating | 600 psig WOG |
| | Close-off pressure Δps | 600 psi |
| | Flow characteristic | modified equal percentage |
| | Leakage rate | ANSI Class VI |
| | Pipe connection | Internal thread NPT (female) |
| | Max Differential Pressure (Steam) | 35 psi |
| | Flow Pattern | 2-way |
| | Controllable flow range | 90° rotation |
| | Cv | 4 |
| | Maximum Inlet Pressure (Steam) | 35 psi [241 kPa] |
| | Maximum Velocity | 15 FPS |
| Materials | Valve body | Bronze B584-C84400 |
| | Housing seal | PTFE |
| | Stem | 316 stainless steel |
| | Stem seal | RPTFE |
| | Seat | RPTFE |
| | Lock nut | stainless steel |
| | Retainer | B16 Brass |
| Suitable actuators | Ball | 316 stainless steel |
| | Non Fail-Safe | LMB(X) GRCB(X) GRB(X) |
| | Spring | LF |

Safety notes



- WARNING: This product can expose you to lead which is known to the State of California to cause cancer and reproductive harm. For more information go to www.p65warnings.ca.gov

Product features

Application This valve is typically used in air handling units on heating or cooling coils, and fan coil unit heating or cooling coils. Some other common applications include Unit Ventilators, VAV Box re-heat coils and bypass loops. This valve is suitable for use in a hydronic system with variable flow.

This valve is designed with MFT functionally which facilitates the use of various control input.

Up to 35 psi steam


1/2" - 2" 600 PSIG WOG, Cold Non-Shock

Federal Specification: WW-V-35C, Type II

Composition: BZ


Style: 3

Flow/Mounting details



Dimensions

| Type | DN | Weight |
|------------|----|-------------------|
| B2050VS-04 | 15 | 0.52 lb [0.24 kg] |




B2050VS..+GRC..N4

| A | B | C | D | E | F |
|-------------|-----------|-------------|-------------|-----------|-----------|
| 14.1" [358] | 2.2" [56] | 10.9" [277] | 10.3" [262] | 3.4" [86] | 3.4" [86] |

On/Off, Floating point, Non fail-safe, 100...240 V



5-year warranty



Technical data

| | | |
|------------------------|------------------------------------|---|
| Electrical data | Nominal voltage | AC 100...240 V |
| | Nominal voltage frequency | 50/60 Hz |
| | Nominal voltage range | AC 85...265 V |
| | Power consumption in operation | 6 W |
| | Power consumption in rest position | 2 W |
| | Transformer sizing | 11 VA |
| | Electrical Connection | 18 AWG appliance cable, 1 m, with 1/2" NPT conduit connector |
| | Overload Protection | electronic throughout 0...90° rotation |
| Functional data | Direction of motion motor | selectable with switch 0/1 |
| | Manual override | under cover |
| | Angle of rotation | 90° |
| | Angle of rotation note | adjustable with mechanical stop |
| | Running Time (Motor) | 35 s / 90° |
| | Running time motor note | constant, independent of load |
| | Noise level, motor | 45 dB(A) |
| | Position indication | Mechanical, 5...20 mm stroke |
| Safety data | Power source UL | Class 2 Supply |
| | Degree of protection IEC/EN | IP66/67 |
| | Degree of protection NEMA/UL | NEMA 4X |
| | Housing | UL Enclosure Type 4X |
| | Agency Listing | cULus acc. to UL60730-1A/-2-14, CAN/CSA E60730-1:02, CE acc. to 2014/30/EU and 2014/35/EU |
| | Quality Standard | ISO 9001 |
| | Ambient humidity | Max. 100% RH |
| | Ambient temperature | -22...122°F [-30...50°C] |
| | Ambient temperature note | -40...50°C [104...122°F] for actuator with integrated heating |
| | Storage temperature | -40...176°F [-40...80°C] |
| | Servicing | maintenance-free |

| | | |
|------------------|--|---------------------------------------|
| Weight | Weight | 6.9 lb [3.1 kg] |
| Materials | Housing material | Die cast aluminium and plastic casing |
| Footnotes | †Rated Impulse Voltage 2.5kV, Type of Action 1.AA, Control Pollution Degree 3. | |

Accessories

| Factory add-on option only | Description | Type |
|----------------------------|------------------------------------|------------|
| | Heater, with adjustable thermostat | ACT_PACK_H |
| | Heater, with adjustable thermostat | ACT_PACK_Y |


Electrical installation

✂ INSTALLATION NOTES

- Ⓐ Actuators with appliance cables are numbered.
- ⚠ Provide overload protection and disconnect as required.
- ⚠ Actuators may be connected in parallel. Power consumption and input impedance must be observed.
- ◆ Meets cULus requirements without the need of an electrical ground connection.
- ⚠ **Warning! Live electrical components!**
During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

Wiring diagrams

On/Off AC 100...240 V



Floating Point AC 100...240 V

