


2-way, Characterized Control Valve, Chrome Plated Brass Ball and Nickel Plated Brass Stem



5-year warranty



## Type overview

|       |    |
|-------|----|
| Type  | DN |
| B215B | 15 |

## Technical data

|                    |                          |                                        |
|--------------------|--------------------------|----------------------------------------|
| Functional data    | Valve size [mm]          | 0.5" [15]                              |
|                    | Fluid                    | chilled or hot water, up to 60% glycol |
|                    | Fluid Temp Range (water) | 0...250°F [-18...120°C]                |
|                    | Body Pressure Rating     | 600 psi                                |
|                    | Close-off pressure Δps   | 200 psi                                |
|                    | Flow characteristic      | equal percentage                       |
|                    | Leakage rate             | 0% for A – AB                          |
|                    | Pipe connection          | Internal thread<br>NPT (female)        |
|                    | Servicing                | maintenance-free                       |
|                    | Flow Pattern             | 2-way                                  |
|                    | Controllable flow range  | 75°                                    |
|                    | Cv                       | 10                                     |
| Materials          | Valve body               | Nickel-plated brass body               |
|                    | Stem                     | nickel-plated brass                    |
|                    | Stem seal                | EPDM (lubricated)                      |
|                    | Seat                     | PTFE                                   |
|                    | Characterized disc       | TEFZEL®                                |
|                    | O-ring                   | EPDM (lubricated)                      |
|                    | Ball                     | chrome plated brass                    |
| Suitable actuators | Non Fail-Safe            | TR<br>LRB(X)                           |
|                    | Spring                   | TFRB(X)<br>LF                          |

## Safety notes




- WARNING: This product can expose you to lead which is known to the State of California to cause cancer and reproductive harm. For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)

## Product features

**Application** This valve is typically used in air handling units on heating or cooling coils, and fan coil unit heating or cooling coils. Some other common applications include Unit Ventilators, VAV box re-heat coils and bypass loops. This valve is suitable for use in a hydronic system with variable flow.



## Flow/Mounting details

Two-way valves should be installed with the disc upstream.





## Dimensions


| Type  | DN | Weight            |
|-------|----|-------------------|
| B215B | 15 | 0.66 lb [0.30 kg] |



Dimensions



On/Off, Floating point, Spring return, 24 V



5-year warranty



## Technical data



|                 |                                    |                                                                                             |
|-----------------|------------------------------------|---------------------------------------------------------------------------------------------|
| Electrical data | Nominal voltage                    | AC/DC 24 V                                                                                  |
|                 | Nominal voltage frequency          | 50/60 Hz                                                                                    |
|                 | Nominal voltage range              | AC 19.2...28.8 V / DC 21.6...28.8 V                                                         |
|                 | Power consumption in operation     | 2.5 W                                                                                       |
|                 | Power consumption in rest position | 1 W                                                                                         |
|                 | Transformer sizing                 | 5 VA                                                                                        |
|                 | Electrical Connection              | 18 GA appliance cable, 3 ft [1 m], with 1/2" NPT conduit connector                          |
|                 | Overload Protection                | electronic throughout 0...95° rotation                                                      |
| Functional data | Position feedback U note           | No Feedback                                                                                 |
|                 | Direction of motion motor          | selectable with switch 0/1                                                                  |
|                 | Direction of motion fail-safe      | reversible with cw/ccw mounting                                                             |
|                 | Angle of rotation                  | 90°                                                                                         |
|                 | Running Time (Motor)               | 150 s / 90°                                                                                 |
|                 | Running time motor note            | constant, independent of load                                                               |
|                 | Running time fail-safe             | <25 s @ -4...122°F [-20...50°C], <60 s @ -22°F [-30°C]                                      |
|                 | Noise level, motor                 | 50 dB(A)                                                                                    |
|                 | Noise level, fail-safe             | 62 dB(A)                                                                                    |
| Safety data     | Position indication                | Mechanical                                                                                  |
|                 | Power source UL                    | Class 2 Supply                                                                              |
|                 | Degree of protection IEC/EN        | IP54                                                                                        |
|                 | Degree of protection NEMA/UL       | NEMA 2                                                                                      |
|                 | Enclosure                          | UL Enclosure Type 2                                                                         |
|                 | Agency Listing                     | cULus acc. To UL 873 and CAN/CSA C22.2 No. 24-93                                            |
|                 | Quality Standard                   | ISO 9001                                                                                    |
|                 | UL 2043 Compliant                  | Suitable for use in air plenums per Section 300.22(C) of the NEC and Section 602 of the IMC |
|                 | Ambient humidity                   | Max. 95% RH, non-condensing                                                                 |
|                 | Ambient temperature                | -22...122°F [-30...50°C]                                                                    |
|                 | Storage temperature                | -40...176°F [-40...80°C]                                                                    |
|                 | Servicing                          | maintenance-free                                                                            |
| Weight          | Weight                             | □                                                                                           |
| Materials       | Housing material                   | galvanized steel                                                                            |

**Technical data**

**Footnotes** †Rated Impulse Voltage 800V, Type of action 1.AA, Control Pollution Degree 3

**Electrical installation**
**✂ INSTALLATION NOTES**

- Ⓐ Actuators with appliance cables are numbered.
- 1 Provide overload protection and disconnect as required.
- 3 Actuators may also be powered by DC 24 V.
- 6 Actuators Hot wire must be connected to the control board common. Only connect common to neg. (-) leg of control circuits. Terminal models (-T) have no-feedback.
- 11 Actuators may be connected in parallel if not mechanically linked. Power consumption and input impedance must be observed.
- ◆ Meets cULus requirements without the need of an electrical ground connection.
- ⚠ **Warning! Live electrical components!**  
During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

**Wiring diagrams**
**Floating Point**

**Floating Point - Triac Source**

**Floating Point - Triac Sink**
