




5-year warranty



Type overview

Type	DN
B262	65

Technical data

Functional data	Valve size [mm]	2.5" [65]
Fluid	chilled or hot water, up to 60% glycol	
Fluid Temp Range (water)	0...212°F [-18...100°C]	
Body Pressure Rating	400 psi	
Close-off pressure Δ ps	100 psi	
Flow characteristic	equal percentage	
Pipe connection type	Internal thread NPT (female)	
Servicing	maintenance-free	
Flow Pattern	2-way	
Leakage rate	0% for A – AB	
Controllable flow range	75°	
Cv	75	
Materials	Valve body	Nickel-plated brass body
Stem	stainless steel	
Stem seal	EPDM (lubricated)	
Seat	PTFE	
Characterized disc	TEFZEL®	
O-ring	EPDM (lubricated)	
Ball	stainless steel	
Suitable actuators	Non-Spring	ARB(X)
Spring	AFRB(X)	

Safety notes




- WARNING: This product can expose you to lead which is known to the State of California to cause cancer and reproductive harm. For more information go to www.p65warnings.ca.gov

Product features

Application	This valve is typically used in air handling units on heating or cooling coils, and fan coil unit heating or cooling coils. Some other common applications include Unit Ventilators, VAV box reheat coils and bypass loops. This valve is suitable for use in a hydronic system with variable flow.
-------------	---

Flow/Mounting details


Two-way valves should be installed with the disc upstream.




Dimensions

Type	DN	Weight
B262	65	8.1 lb [3.7 kg]


ARB, ARX		A 10.1" [257]	B 5.6" [141]	C 8.0" [203]	D 6.0" [152]	E 2.8" [71]	F 2.8" [71]	H1 1.9" [48]
		A 11.5" [293]	B 5.6" [141]	C 8.6" [219]	D 6.6" [168]	E 2.0" [51]	F 2.0" [51]	
AFRB, AFRX		A 11.5" [293]	B 5.6" [141]	C 8.6" [219]	D 6.6" [168]	E 2.0" [51]	F 2.0" [51]	
		A 9.9" [251]	B 4.2" [107]	C 8.1" [206]	D 6.1" [155]	E 2.3" [58]	F 2.3" [58]	H1 0.8" [20]
ARQB, ARQX		A 9.9" [251]	B 4.2" [107]	C 8.1" [206]	D 6.1" [155]	E 2.3" [58]	F 2.3" [58]	H1 0.8" [20]
		A 9.9" [251]	B 4.2" [107]	C 8.1" [206]	D 6.1" [155]	E 2.3" [58]	F 2.3" [58]	H2 0.6" [15]




AFRB N4, AFRX N4



A	B	D	E	F
11.4" [289]	5.6" [141]	8.0" [203]	2.4" [62]	2.4" [62]



ARB N4, ARX N4, NRB N4, NRX N4



A	B	D	E	F
11.4" [289]	5.6" [141]	8.0" [203]	3.1" [80]	3.1" [80]



5-year warranty



Technical data

Electrical data	Nominal voltage	AC/DC 24 V
	Nominal voltage frequency	50/60 Hz
	Nominal voltage range	AC 19.2...28.8 V / DC 21.6...28.8 V
	Power consumption in operation	15 W
	Power consumption in rest position	1.5 W
	Transformer sizing	23 VA
	Electrical Connection	18 GA plenum cable, 1 m, with 1/2" NPT conduit connector (3 m and 5 m available)
	Overload Protection	electronic throughout 0...95° rotation
Functional data	Direction of motion motor	selectable with switch 0/1
	Manual override	external push button
	Angle of rotation	90°
	Angle of rotation note	adjustable with mechanical stop
	Running Time (Motor)	10 s / 90°
	Running time motor variable	10 or 15 s
	Noise level, motor	52 dB(A)
	Position indication	Mechanical, pluggable
Safety data	Power source UL	Class 2 Supply
	Degree of protection IEC/EN	IP54
	Degree of protection NEMA/UL	NEMA 2
	Enclosure	UL Enclosure Type 2
	Agency Listing	cULus acc. to UL60730-1A-2-14, CAN/CSA E60730-1:02 CE acc. to 2014/30/EU and 2014/35/EU
	Quality Standard	ISO 9001
	UL 2043 Compliant	Suitable for use in air plenums per Section 300.22(C) of the NEC and Section 602 of the IMC
	Ambient humidity	Max. 95% RH, non-condensing
	Ambient temperature	-22...122°F [-30...50°C]
	Storage temperature	-40...176°F [-40...80°C]
	Servicing	maintenance-free
Weight	Weight	3.1 lb [1.4 kg]
Materials	Housing material	Galvanized steel and plastic housing
Footnotes	†Rated Impulse Voltage 800V, Type action 1.B, Control Pollution Degree 3.	

Accessories

Electrical accessories	Description	Type
	Battery backup system, for non-spring return models	NSV24 US
	Battery, 12 V, 1.2 Ah (two required)	NSV-BAT

Electrical installation

 **INSTALLATION NOTES**

-  1 Provide overload protection and disconnect as required.
-  2 Actuators may be connected in parallel. Power consumption and input impedance must be observed.
-  3 Actuators may also be powered by DC 24 V.
-  18 Actuators with plenum cable do not have numbers; use color codes instead.
-  Meets cULus requirements without the need of an electrical ground connection.
-  **Warning! Live electrical components!**
During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.



Wiring diagrams

On/Off

