

3-way Changeover/ Diverting, Chrome Plated Brass Ball and Nickel Plated Brass Stem



2-year warranty

Picture may differ from product

Type overview

Type	DN
B332L	1 1/4" [32]


Technical data

	Functional data	Valve size [mm]	1.25" [32]
Fluid		chilled or hot water, up to 60% glycol	
Fluid Temp Range (water)		0...250°F [-18...120°C]	
Body Pressure Rating		400 psi	
Close-off pressure Δ ps		200 psi	
Flow characteristic		modified linear	
Leakage rate		0%	
Pipe connection		Internal thread NPT (female)	
Servicing		maintenance-free	
Flow Pattern		3-way Changeover/ Diverting	
Controllable flow range		75°	
Cv		34	
	Materials	Valve body	Nickel-plated brass body
	Stem		nickel-plated brass
	Seat		PTFE
	Ball		chrome plated brass
	Suitable actuators	Non Fail-Safe	NRB(X)
	Spring		AFRB(X)

Product features



Application This valve is typically used in air handling units on heating or cooling coils, and fan coil unit heating or cooling coils. Some other common applications include Unit Ventilators, VAV box re-heat coils and bypass loops. This valve is suitable for use as diverting or change over valve.

Flow/Mounting details





Dimensions

Type	DN	Weight
B332L	1 1/4" [32]	2.6 lb [1.2 kg]



A	B	C	D	E	F	H1	H2
4.9" [125]	2.7" [69]	6.8" [172]	5.5" [140]	1.8" [46]	2.1" [54]	0.8" [20]	0.6" [15]



A	B	C	D	E	F
10.6" [269]	4.0" [101]	6.9" [175]	5.7" [146]	2.1" [54]	1.3" [33]



5-year warranty



Technical data

Electrical data	Nominal voltage	AC/DC 24 V
Nominal voltage frequency	50/60 Hz	
Nominal voltage range	AC 19.2...28.8 V / DC 21.6...28.8 V	
Power consumption in operation	7.5 W	
Power consumption in rest position	3 W	
Transformer sizing	10 VA	
Auxiliary switch	2x SPDT, 1 mA...3 A (0.5 A inductive), DC 5 V...AC 250 V, one set at 10°, one adjustable 10...90°	
Switching capacity auxiliary switch	1 mA...3 A (0.5 A inductive), DC 5 V...AC 250 V	
Electrical Connection	(2) 18 GA appliance cables, 1 m, with 1/2" NPT conduit connectors	
Overload Protection	electronic throughout 0...95° rotation	
Functional data	Operating range Y	2...10 V
Operating range Y note	4...20 mA w/ ZG-R01 (500 Ω, 1/4 W resistor)	
Input impedance	100 kΩ for 2...10 V (0.1 mA), 500 Ω for 4...20 mA, 1500 Ω for PWM, On/Off and Floating point	
Operating range Y variable	Start point 0.5...30 V End point 2.5...32 V	
Operating modes optional	variable (VDC, PWM, on/off, floating point)	
Position feedback U	2...10 V	
Position feedback U note	Max. 0.5 mA	
Position feedback U variable	VDC variable	
Direction of motion motor	selectable with switch	
Direction of motion fail-safe	reversible with cw/ccw mounting	
Manual override	5 mm hex crank (3/16" Allen), supplied	
Angle of rotation	90°	
Running Time (Motor)	150 s / 90°	
Running time motor variable	70...220 s	
Running time fail-safe	<20 s @ 20°C	
Adaptation Setting Range	off (default)	
Override control	MIN (minimum position) = 0% MID (intermediate position) = 50% MAX (maximum position) = 100%	
Noise level, motor	45 dB(A)	
Noise level, fail-safe	62 dB(A)	
Position indication	Mechanical	
Safety data	Power source UL	Class 2 Supply
Degree of protection IEC/EN	IP54	
Degree of protection NEMA/UL	NEMA 2	
Enclosure	UL Enclosure Type 2	

Safety data	Agency Listing	cULus acc. to UL60730-1A/-2-14, CAN/CSA E60730-1:02 CE acc. to 2014/30/EU and 2014/35/EU
Quality Standard	ISO 9001	
UL 2043 Compliant	Suitable for use in air plenums per Section 300.22(C) of the NEC and Section 602 of the IMC	
Ambient humidity	Max. 95% RH, non-condensing	
Ambient temperature	-22...122°F [-30...50°C]	
Storage temperature	-40...176°F [-40...80°C]	
Servicing	maintenance-free	
Weight	Weight	5.4 lb [2.4 kg]
Materials	Housing material	Galvanized steel and plastic housing

Footnotes †Rated Impulse Voltage 800V, Type of action 1.AA, Control Pollution Degree 3

Accessories

	Gateways	Description	Type
	Gateway MP to BACnet MS/TP		UK24BAC
	Gateway MP to Modbus RTU		UK24MOD
	Gateway MP to LonWorks		UK24LON
	Electrical accessories	Description	Type
	Service tool, with ZIP-USB function, for programmable and communicative Belimo actuators, VAV controller and HVAC performance devices		ZTH US
	Tools	Description	Type
	Connecting cable 10 ft [3 m], A: RJ11 6/4 ZTH EU, B: 3-pin Weidmüller and supply connection		ZK4-GEN
	Service tool, with ZIP-USB function, for programmable and communicative Belimo actuators, VAV controller and HVAC performance devices		ZTH US

Electrical installation

INSTALLATION NOTES


-  Actuators with appliance cables are numbered.
-  Provide overload protection and disconnect as required.
-  Actuators may also be powered by DC 24 V.
-  Two built-in auxiliary switches (2x SPDT), for end position indication, interlock control, fan startup, etc.
-  Only connect common to negative (-) leg of control circuits.
-  A 500 Ω resistor (ZG-R01) converts the 4...20 mA control signal to 2...10 V.
-  Control signal may be pulsed from either the Hot (Source) or Common (Sink) 24 V line.
-  For triac sink the Common connection from the actuator must be connected to the Hot connection of the controller. Position feedback cannot be used with a triac sink controller; the actuator internal common reference is not compatible.
-  Actuators may be controlled in parallel. Current draw and input impedance must be observed.
-  Master-Slave wiring required for piggy-back applications. Feedback from Master to control input(s) of Slave(s).
-  Meets cULus requirements without the need of an electrical ground connection.
-  **Warning! Live electrical components!**
During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

⚠ Apply only AC line voltage or only UL-Class 2 voltage to the terminals of auxiliary switches. Mixed or combined operation of line voltage/safety extra low voltage is not allowed.

Wiring diagrams


On/Off

24 VAC Transformer




Floating Point

24 VAC Transformer (AC Only)




VDC/mA Control




PWM Control


24 VAC Transformer (AC only)



Override Control



Primary - Secondary



Auxiliary Switches

