

3-way Mixing/Diverting, Characterized Control Valve, Stainless Steel Ball and Stem



Picture may differ from product



5-year warranty



## Type overview

### Type

B341

### DN

1 1/2" [40]

## Technical data

|                           |                          |                                                                        |
|---------------------------|--------------------------|------------------------------------------------------------------------|
| <b>Functional data</b>    | Valve size [mm]          | 1.5" [40]                                                              |
|                           | Fluid                    | chilled or hot water, up to 60% glycol                                 |
|                           | Fluid Temp Range (water) | 0...250°F [-18...120°C]                                                |
|                           | Body Pressure Rating     | 400 psi                                                                |
|                           | Close-off pressure Δps   | 200 psi                                                                |
|                           | Flow                     | A-port: as stated in chart B-port: 70% of A – AB Cv                    |
|                           | Flow characteristic      | A-port equal percentage, B-port modified for constant common port flow |
|                           | Leakage rate             | 0% for A – AB, <2.0% for B – AB                                        |
|                           | Pipe connection          | Internal thread<br>NPT (female)                                        |
|                           | Servicing                | maintenance-free                                                       |
|                           | Flow Pattern             | 3-way Mixing/Diverting                                                 |
|                           | Controllable flow range  | 75°                                                                    |
|                           | Cv                       | 46                                                                     |
| <b>Materials</b>          | Valve body               | Nickel-plated brass body                                               |
|                           | Stem                     | stainless steel                                                        |
|                           | Stem seal                | EPDM (lubricated)                                                      |
|                           | Seat                     | PTFE                                                                   |
|                           | Characterized disc       | Stainless steel                                                        |
|                           | O-ring                   | EPDM (lubricated)                                                      |
|                           | Ball                     | stainless steel                                                        |
| <b>Suitable actuators</b> | Non Fail-Safe            | ARB(X)<br>ARQB(X)<br>ARB(X) N4                                         |
|                           | Spring                   | AFRB(X)                                                                |

## Safety notes



- WARNING: This product can expose you to lead which is known to the State of California to cause cancer and reproductive harm. For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)

## Product features

**Application** This valve is typically used in air handling units on heating or cooling coils, and fan coil unit heating or cooling coils. Some other common applications include Unit Ventilators, VAV box re-heat coils and bypass loops. This valve is suitable for use in a hydronic system with variable or constant flow.


## Flow/Mounting details

This valve is not suitable for use as a change over valve.




## Dimensions

| Type | DN          | Weight          |
|------|-------------|-----------------|
| B341 | 1 1/2" [40] | 3.7 lb [1.7 kg] |




ARB, ARX

| A           | B          | C          | D          | E          | F         | H1        | H2        |
|-------------|------------|------------|------------|------------|-----------|-----------|-----------|
| 10.0" [254] | 4.4" [112] | 7.2" [184] | 5.7" [146] | 1.77" [44] | 2.3" [58] | 0.8" [20] | 1.2" [30] |



ARB N4, ARX N4


| A           | B          | C          | D          | E         | F         |
|-------------|------------|------------|------------|-----------|-----------|
| 11.4" [289] | 4.4" [112] | 9.3" [236] | 7.8" [198] | 3.1" [80] | 3.1" [80] |



ARQB, ARQX


| A          | B          | C          | D          | E         | F         | H1        | H2        |
|------------|------------|------------|------------|-----------|-----------|-----------|-----------|
| 9.9" [251] | 4.4" [112] | 7.8" [199] | 6.3" [161] | 2.3" [58] | 2.3" [58] | 0.8" [20] | 0.8" [20] |

## Dimensions



AFRB, AFRX

| A           | B          | C          | D          | E         | F         |
|-------------|------------|------------|------------|-----------|-----------|
| 10.8" [275] | 4.4" [112] | 7.9" [201] | 6.4" [162] | 2.3" [58] | 2.3" [58] |




AFRB N4, AFRX N4

| A           | B          | C           | D          | E         | F         |
|-------------|------------|-------------|------------|-----------|-----------|
| 13.0" [330] | 4.4" [112] | 11.2" [284] | 9.7" [246] | 3.7" [95] | 3.7" [95] |

On/Off, Floating point, Non fail-safe, 24 V



5-year warranty



## Technical data

|                 |                                    |                                                                                             |
|-----------------|------------------------------------|---------------------------------------------------------------------------------------------|
| Electrical data | Nominal voltage                    | AC/DC 24 V                                                                                  |
|                 | Nominal voltage frequency          | 50/60 Hz                                                                                    |
|                 | Nominal voltage range              | AC 19.2...28.8 V / DC 21.6...28.8 V                                                         |
|                 | Power consumption in operation     | 2.5 W                                                                                       |
|                 | Power consumption in rest position | 0.5 W                                                                                       |
|                 | Transformer sizing                 | 5.5 VA                                                                                      |
|                 | Electrical Connection              | 18 AWG plenum cable, 1 m, with 1/2" NPT conduit connector                                   |
|                 | Overload Protection                | electronic throughout 0...90° rotation                                                      |
| Functional data | Direction of motion motor          | selectable with switch 0/1                                                                  |
|                 | Manual override                    | external push button                                                                        |
|                 | Angle of rotation                  | 90°                                                                                         |
|                 | Angle of rotation note             | adjustable with mechanical stop                                                             |
|                 | Running Time (Motor)               | 90 s / 90°                                                                                  |
|                 | Noise level, motor                 | 45 dB(A)                                                                                    |
|                 | Position indication                | Mechanical, pluggable                                                                       |
| Safety data     | Power source UL                    | Class 2 Supply                                                                              |
|                 | Degree of protection NEMA/UL       | NEMA 2                                                                                      |
|                 | Housing                            | UL Enclosure Type 2                                                                         |
|                 | Agency Listing                     | cULus acc. to UL60730-1A/-2-14, CAN/CSA E60730-1:02, CE acc. to 2014/30/EU                  |
|                 | Quality Standard                   | ISO 9001                                                                                    |
|                 | UL 2043 Compliant                  | Suitable for use in air plenums per Section 300.22(C) of the NEC and Section 602 of the IMC |
|                 | Ambient humidity                   | Max. 95% RH, non-condensing                                                                 |
|                 | Ambient temperature                | -22...122°F [-30...50°C]                                                                    |
|                 | Storage temperature                | -40...176°F [-40...80°C]                                                                    |
|                 | Servicing                          | maintenance-free                                                                            |
| Weight          | Weight                             | 2.2 lb [1 kg]                                                                               |
| Materials       | Housing material                   | Galvanized steel and plastic housing                                                        |

**Footnotes** †Rated Impulse Voltage 800V, Type action 1.B, Control Pollution Degree 3.

## Electrical installation

### ✂ INSTALLATION NOTES


- 1 Provide overload protection and disconnect as required.
- 3 Actuators may also be powered by DC 24 V.
- 6 Actuators Hot wire must be connected to the control board common. Only connect common to neg. (-) leg of control circuits. Terminal models (-T) have no-feedback.
- 18 Actuators with plenum cable do not have numbers; use color codes instead.
- ◆ Meets cULus requirements without the need of an electrical ground connection.

### ⚠ Warning! Live electrical components!


During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

### Wiring diagrams


On/Off



Floating Point




24 VAC Transformer



Floating Point - Triac Sink

24 VAC Transformer



## Dimensions

