

3-way Changeover/ Diverting, Chrome Plated Brass Ball and Nickel Plated Brass Stem



2-year warranty

Picture may differ from product

## Type overview

Type	DN
B350L	2" [50]


## Technical data

	Functional data	Valve size [mm]	2" [50]
Fluid		chilled or hot water, up to 60% glycol	
Fluid Temp Range (water)		0...250°F [-18...120°C]	
Body Pressure Rating		400 psi	
Close-off pressure $\Delta$ ps		200 psi	
Flow characteristic		modified linear	
Leakage rate		0%	
Pipe connection		Internal thread NPT (female)	
Servicing		maintenance-free	
Flow Pattern		3-way Changeover/ Diverting	
Controllable flow range		75°	
Cv		87	
	Materials	Valve body	Nickel-plated brass body
	Stem		nickel-plated brass
	Seat		PTFE
	Ball		chrome plated brass
	Suitable actuators	Non Fail-Safe	ARB(X)
	Spring		AFRB(X)

## Product features



**Application** This valve is typically used in air handling units on heating or cooling coils, and fan coil unit heating or cooling coils. Some other common applications include Unit Ventilators, VAV box re-heat coils and bypass loops. This valve is suitable for use as diverting or change over valve.

## Flow/Mounting details




## Dimensions

Type	DN	Weight
B350L	2" [50]	5.7 lb [2.6 kg]



On/Off, Spring return, 24...240 V



## Technical data

<b>Electrical data</b>	Nominal voltage	AC 24...240 V / DC 24...125 V
	Nominal voltage frequency	50/60 Hz
	Nominal voltage range	AC 19.2...264 V / DC 21.6...137.5 V
	Power consumption in operation	7 W
	Power consumption in rest position	3.5 W
	Transformer sizing	18 VA
	Electrical Connection	18 GA appliance cable, 3 ft [1 m], with 1/2" NPT conduit connector
	Overload Protection	electronic throughout 0...95° rotation
<b>Functional data</b>	Direction of motion motor	selectable by ccw/cw mounting
	Direction of motion fail-safe	reversible with cw/ccw mounting
	Manual override	5 mm hex crank (3/16" Allen), supplied
	Angle of rotation	90°
	Running Time (Motor)	75 s / 90°
	Running time fail-safe	<20 s
	Noise level, motor	45 dB(A)
	Noise level, fail-safe	62 dB(A)
	Position indication	Mechanical
<b>Safety data</b>	Power source UL	Class 2 Supply
	Degree of protection IEC/EN	IP54
	Degree of protection NEMA/UL	NEMA 2
	Enclosure	UL Enclosure Type 2
	Agency Listing	cULus acc. to UL60730-1A/-2-14, CAN/CSA E60730-1:02 CE acc. to 2014/30/EU and 2014/35/EU
	Quality Standard	ISO 9001
	UL 2043 Compliant	Suitable for use in air plenums per Section 300.22(C) of the NEC and Section 602 of the IMC
	Ambient humidity	Max. 95% RH, non-condensing
	Ambient temperature	-22...122°F [-30...50°C]
	Storage temperature	-40...176°F [-40...80°C]
	Servicing	maintenance-free
<b>Weight</b>	Weight	5.4 lb [2.4 kg]
<b>Materials</b>	Housing material	Galvanized steel and plastic housing

## Technical data

Footnotes <sup>t</sup>Rated Impulse Voltage 800V, Type of action 1.AA, Control Pollution Degree 3

## Electrical installation

 **INSTALLATION NOTES**

-  A Actuators with appliance cables are numbered.
-  UP Universal Power Supply (UP) models can be supplied with AC 24...240 V, or DC 24...125 V.
-  1 Provide overload protection and disconnect as required.
-  45 Actuators may be powered in parallel. Power consumption must be observed.
-  48 Parallel wiring required for piggy-back applications.
-  Meets cULus requirements without the need of an electrical ground connection.
-  **Warning! Live electrical components!**  
During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

## Wiring diagrams

On/Off

24 to 240 VAC

