



5-year warranty

Type overview

Type	DN
B6400S-186-250	100

Technical data

Functional data	Valve size [mm]	4" [100]
Fluid		chilled or hot water, up to 60% glycol
Fluid Temp Range (water)		0...250°F [-18...120°C]
Body Pressure Rating		ANSI Class 250, raised-face
Close-off pressure Δp		310 psi
Flow characteristic		equal percentage
Pipe connection type		Flange for use with ASME/ANSI class 250
Servicing		maintenance-free
Maximum differential pressure (water)		50 psi [345 kPa]
Flow Pattern		2-way
Leakage rate		0% for A – AB
Controllable flow range		75°
Cv		186
Materials	Valve body	Cast iron - GG 25
	Stem	stainless steel
	Stem seal	EPDM (lubricated)
	Seat	PTFE
	Characterized disc	stainless steel
	O-ring	EPDM (lubricated)
	Ball	stainless steel
Suitable actuators	Non-Spring	GRB(X)
	Electrical fail-safe	GKRB(X)

Safety notes




- WARNING: This product can expose you to lead which is known to the State of California to cause cancer and reproductive harm. For more information go to www.p65warnings.ca.gov

Product features


Application	This valve is typically used in air handling units on heating or cooling coils, and fan coil unit heating or cooling coils. Some other common applications include Unit Ventilators, VAV box reheat coils and bypass loops. This valve is suitable for use in a hydronic system with variable flow.
-------------	---

Flow/Mounting details



Upstream A
Downstream AB

Flow Direction



Dimensions

Type

B6400S-186-250

DN


100

Weight


70 lb [32 kg]

GRB, GRX	A	B	C	D	E	F	G	I	Number of Bolt Holes
									8
GKRB, GKRX	A	B	C	D	E	F	G	I	Number of Bolt Holes
GRX, GKRX	A	B	C	D	E	F	G	I	Number of Bolt Holes

GKRB, GKRX	A	B	C	D	E	F	G	I	Number of Bolt Holes
									8
GRX, GKRX	A	B	C	D	E	F	G	I	Number of Bolt Holes



A	B	C	D	E	F	G	I	Number of Bolt Holes
15.0" [381]	8.3" [210]	16.3" [415]	12.6" [321]	4.4" [113]	4.4" [113]	7.9" [200]	0.9" [22]	8



A	B	C	D	E	F	G	I	Number of Bolt Holes
15.0" [381]	8.3" [210]	16.3" [415]	12.6" [321]	4.4" [113]	4.4" [113]	7.9" [200]	0.9" [22]	8

MFT/programmable, Electronic fail-safe, 24 V



5-year warranty



Technical data

Electrical data	Nominal voltage	AC/DC 24 V
	Nominal voltage frequency	50/60 Hz
	Nominal voltage range	AC 19.2...28.8 V / DC 21.6...28.8 V
	Power consumption in operation	12 W
	Power consumption in rest position	3 W
	Transformer sizing	21 VA
	Electrical Connection	18 AWG plenum cable, 1 m, with 1/2" NPT conduit connector
	Overload Protection	electronic throughout 0...90° rotation
Functional data	Operating range Y	2...10 V
	Operating range Y note	4...20 mA w/ ZG-R01 (500 Ω, 1/4 W resistor)
	Input impedance	100 kΩ for 2...10 V (0.1 mA), 500 Ω for 4...20 mA, 1500 Ω for PWM, On/Off and Floating point
	Operating range Y variable	Start point 0.5...30 V End point 2.5...32 V
	Operating modes optional	variable (VDC, on/off, floating point)
	Position feedback U	2...10 V
	Position feedback U note	Max. 0.5 mA
	Position feedback U variable	VDC variable
	Bridging time (PF)	2 s
	Bridging time (PF) variable	0...10 s
	Pre-charging time	5...20 s
	Direction of motion motor	selectable with switch 0/1
	Direction of motion fail-safe	reversible with switch
	Manual override	under cover
	Angle of rotation	Max. 95°
	Angle of rotation note	adjustable with mechanical stop
	Running Time (Motor)	150 s / 90°
	Running time motor variable	90...150 s
	Running time fail-safe	<35 s
	Noise level, motor	52 dB(A)
	Noise level, fail-safe	61 dB(A)

Functional data	Position indication	Mechanical, 30...65 mm stroke
Safety data		
Power source UL	Class 2 Supply	
Degree of protection IEC/EN	IP66/67	
Degree of protection NEMA/UL	NEMA 4X	
Housing	UL Enclosure Type 4X	
Agency Listing	cULus acc. to UL60730-1A/-2-14, CAN/CSA E60730-1:02, CE acc. to 2014/30/EU and 2014/35/EU	
Quality Standard	ISO 9001	
Ambient humidity	Max. 100% RH	
Ambient temperature	-22...122°F [-30...50°C]	
Ambient temperature note	-40...50°C [104...122°F] for actuator with integrated heating	
Storage temperature	-40...176°F [-40...80°C]	
Servicing	maintenance-free	
Weight	Weight	7.5 lb [3.4 kg]
Materials	Housing material	Die cast aluminium and plastic casing

Footnotes †Rated Impulse Voltage 800V, Type of action 1.AA, Control Pollution Degree 3

Product features

Bridging time Power failures can be bridged up to a maximum of 10 s. In the event of a power failure, the actuator will remain stationary in accordance with the set bridging time. If the power failure is greater than the set bridging time, the actuator will move into the selected fail-safe position. The bridging time set at the factory is 2 s. It can be modified on site in operation by means of the Belimo service tool MFT-P. Settings: The rotary knob must not be set to the "PROG FAIL-SAFE" position! For retroactive adjustments of the bridging time with the Belimo service tool MFT-P or with the ZTH EU adjustment and diagnostic device only the values need to be entered.

Accessories

Gateways	Description	Type
Gateway MP to BACnet MS/TP	UK24BAC	
Gateway MP to Modbus RTU	UK24MOD	
Gateway MP to LonWorks	UK24LON	
Electrical accessories	Description	Type
Feedback potentiometer 140 Ω add-on, grey	P140A GR	
Feedback potentiometer 500 Ω add-on, grey	P500A GR	
Feedback potentiometer 1 kΩ add-on, grey	P1000A GR	
Feedback potentiometer 2.8 kΩ add-on, grey	P2800A GR	
Feedback potentiometer 5 kΩ add-on, grey	P5000A GR	
Feedback potentiometer 10 kΩ add-on, grey	P10000A GR	
Auxiliary switch 1x SPDT add-on	S1A	
Auxiliary switch 2x SPDT add-on	S2A	
Service tool, with ZIP-USB function, for configurable and communicative Belimo actuators, VAV controller and HVAC performance devices	ZTH US	

Accessories

Tools	Description	Type
	Connecting cable 10 ft [3 m], A: RJ11 6/4 ZTH EU, B: 3-pin Weidmüller and supply connection	ZK4-GEN
	Service tool, with ZIP-USB function, for configurable and communicative Belimo actuators, VAV controller and HVAC performance devices	ZTH US
Factory add-on option only	Description	Type
	Heater, with adjustable thermostat	ACT_PACK_H


Electrical installation

☒ INSTALLATION NOTES


- Ⓐ Actuators with appliance cables are numbered.
- Ⓑ Provide overload protection and disconnect as required.
- Ⓒ Actuators may also be powered by DC 24 V.
- Ⓓ Only connect common to negative (-) leg of control circuits.
- Ⓔ A 500 Ω resistor (ZG-R01) converts the 4...20 mA control signal to 2...10 V.
- Ⓕ Control signal may be pulsed from either the Hot (Source) or Common (Sink) 24 V line.
- Ⓖ For triac sink the Common connection from the actuator must be connected to the Hot connection of the controller. Position feedback cannot be used with a triac sink controller; the actuator internal common reference is not compatible.
- Ⓗ IN4004 or IN4007 diode. (IN4007 supplied, Belimo part number 40155).
- Ⓘ Actuators are provided with a numbered screw terminal strip instead of a cable.
- Ⓛ Actuators may be controlled in parallel. Current draw and input impedance must be observed.
- Ⓜ Master-Slave wiring required for piggy-back applications. Feedback from Master to control input(s) of Slave(s).
- Ⓝ Meets cULus requirements without the need of an electrical ground connection.
- !**Warning! Live electrical components!**
During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

Wiring diagrams

On/Off




Floating Point




Electrical installation

Wiring diagrams


VDC/mA Control




PWM Control



Override Control



Primary - Secondary



NEMA 4 Heater

