

Carbon Steel Body, Hardened Chrome Plated,
Stainless Steel Ball and Stem



2-year warranty

Type overview

Type	DN
B6400VB-350	100

Technical data


	Functional data	
	Valve size [mm]	4" [100]
	Fluid	chilled or hot water, up to 60% glycol, steam
	Fluid Temp Range (water)	-22...380°F [-30...193°C]
	Fluid Temp Range (steam)	-22...365°F [-30...185°C]
	Body Pressure Rating	ANSI Class 150
	Close-off pressure Δps	250 psi
	Flow characteristic	equal percentage
	Servicing	repack/rebuild kits available
	Rangeability Sv	300:1
	Maximum differential pressure (water)	150 psi
	Max Differential Pressure (Steam)	100 psi
	Close-Off Pressure (Steam)	150 psi
	Flow Pattern	2-way
	Leakage rate	ANSI Class IV
	Controllable flow range	75°
	Cv	350
	Maximum Inlet Pressure (Steam)	150 psi
	Materials	
	Valve body	WCC grade carbon steel
	Body finish	matt black body finish
	Stem	stainless steel
	Stem seal	PTFE V-ring
	Seat	PTFE
	Pipe connection	125/150 lb flanged, ASME/ANSI b16.1/b16.5
	Ball	stainless steel
	Suitable actuators	
	Non-Spring	GMB(X) PRB(X)
	Spring	EFB(X)
	Electrical fail-safe	PKRB(X) GKB(X)

Product features


Product features	Fast quarter turn open or closed operation, stainless-steel ball and stem, positive isolation, two-piece body construction


Application

This valve is typically used in air handling units on heating or cooling coils, and fan coil unit heating or cooling coils. Some other common applications include Unit Ventilators, VAV box reheat coils and bypass loops. This valve is suitable for use in a hydronic system with variable flow.

Flow/Mounting details**Dimensions**


Type	DN	Weight
B6400VB-350	100	57.32 lb [26 kg]





B6VB-GM

A	B	C	D	E	F	Number of Bolt Holes
12.6" [320]	9.0" [229]	18.2" [463]	13.1" [334]	4.5" [114]	4.5" [114]	8



B6VB-PR

A	B	C	D	E	F	Number of Bolt Holes
12.2" [310]	9.0" [229]	18.2" [463]	13.1" [334]	4.5" [114]	4.5" [114]	8



5-year warranty

**Technical data**

Electrical data	Nominal voltage	AC/DC 24 V
Nominal voltage frequency	50/60 Hz	
Power consumption in operation	12 W	
Power consumption in rest position	3 W	
Transformer sizing	21 VA (class 2 power source)	
Electrical Connection	18 GA plenum cable with 1/2" conduit connector, degree of protection NEMA 2 / IP54, 3 ft [1 m] 10 ft [3 m] and 16ft [5 m]	
Overload Protection	electronic throughout 0...95° rotation	
Functional data		
Operating range Y	2...10 V	
Operating range Y note	4...20 mA w/ ZG-R01 (500 Ω, 1/4 W resistor)	
Input Impedance	100 kΩ for 2...10 V (0.1 mA), 500 Ω for 4...20 mA, 1500 Ω for PWM, On/Off and Floating point	
Operating range Y variable	Start point 0.5...30 V End point 2.5...32 V	
Options positioning signal	variable (VDC, on/off, floating point)	
Position feedback U	2...10 V	
Position feedback U note	Max. 0.5 mA	
Position feedback U variable	VDC variable	
Bridging time (PF)	2 s	
Bridging time (PF) variable	0...10 s	
Pre-charging time	5...20 s	
Direction of motion motor	selectable with switch 0/1	
Direction of motion fail-safe	reversible with switch	
Manual override	external push button	
Angle of rotation	Max. 95°	
Angle of rotation note	adjustable with mechanical stop	
Running Time (Motor)	150 s / 90°	
Running time motor variable	95...150 s	
Running time fail-safe	<35 s	
Noise level, motor	52 dB(A)	
Noise level, fail-safe	61 dB(A)	
Position indication	Mechanically, 30...65 mm stroke	
Safety data		
Degree of protection IEC/EN	IP54	
Degree of protection NEMA/UL	NEMA 2	
Enclosure	UL Enclosure Type 2	

Safety data	Agency Listing	cULus acc. to UL60730-1A/-2-14, CAN/CSA E60730-1:02, CE acc. to 2014/30/EU and 2014/35/EU; Listed to UL 2043 - suitable for use in air plenums per Section 300.22(c) of the NEC and Section 602.2 of the IMC
	Quality Standard	ISO 9001
	Ambient temperature	-22...122°F [-30...50°C]
	Storage temperature	-40...176°F [-40...80°C]
	Ambient humidity	Max. 95% RH, non-condensing
	Servicing	maintenance-free
Materials	Housing material	Galvanized steel and plastic housing

Footnotes †Rated Impulse Voltage 800V, Type of action 1.AA, Control Pollution Degree 3

Product features

Bridging time Electrical interruptions can be bridged up to a maximum of 10 s. In the event of a power failure, the actuator will remain stationary in accordance with the set bridging time. If the power failure is greater than the set bridging time, then the actuator will move into the selected fail-safe position. The bridging time set ex-works is 2 s. This can be modified on site in operation with the use of the Belimo service tool MFT-P. Settings: The rotary knob must not be set to the "PROG FAIL-SAFE" position! For retroactive adjustments of the bridging time with the Belimo service tool MFT-P or with the ZTH EU adjustment and diagnostic device only the values need to be entered.

Accessories

Electrical accessories	Description	Type
Feedback potentiometer 140 Ω add-on, grey	P140A GR	
Feedback potentiometer 500 Ω add-on, grey	P500A GR	
Feedback potentiometer 1 kΩ add-on, grey	P1000A GR	
Feedback potentiometer 2.8 kΩ add-on, grey	P2800A GR	
Feedback potentiometer 5 kΩ add-on, grey	P5000A GR	
Feedback potentiometer 10 kΩ add-on, grey	P10000A GR	
Auxiliary switch 1 x SPDT add-on	S1A	
Auxiliary switch 2 x SPDT add-on	S2A	
Service Tool, with ZIP-USB function, for programmable and communicative Belimo actuators, VAV controller and HVAC performance devices	ZTH US	

Electrical installation

INSTALLATION NOTES






-  A Actuators with appliance cables are numbered.
-  1 Provide overload protection and disconnect as required.
-  3 Actuators may also be powered by DC 24 V.
-  5 Only connect common to negative (-) leg of control circuits.
-  7 A 500 Ω resistor (ZG-R01) converts the 4...20 mA control signal to 2...10 V.
-  8 Control signal may be pulsed from either the Hot (Source) or Common (Sink) 24 V line.
-  10 For triac sink the Common connection from the actuator must be connected to the Hot connection of the controller. Position feedback cannot be used with a triac sink controller; the actuator internal common reference is not compatible.
-  12 IN4004 or IN4007 diode. (IN4007 supplied, Belimo part number 40155).
-  46 Actuators may be controlled in parallel. Current draw and input impedance must be observed.
-  47 Master-Slave wiring required for piggy-back applications. Feedback from Master to control input(s) of Slave(s).
-  Meets cULus requirements without the need of an electrical ground connection.

**Warning! Live electrical components!**

During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

Wiring diagrams

On/Off

24 VAC Transformer**Floating Point****24 VAC Transformer (AC Only)****VDC/mA Control****24 VAC Transformer****PWM Control****24 VAC Transformer (AC only)****Override Control****24 VAC Transformer (AC Only)****Master - Slave**