

NPT-Threaded Globe Valves

- chilled or hot water, up to 60% glycol, steam
- ANSI Class 250, up to 400 psi below 150°F
- repack kits available
- ANSI Class VI



5-year warranty

Type overview

Type	DN
G215S-F	15

Technical data

Functional data	Valve size [mm]	0.5" [15]
Fluid	chilled or hot water, up to 60% glycol, steam	
Fluid Temp Range (water)	20...338°F [-7...170°C]	
Fluid Temp Range (steam)	32...338°F [0...170°C]	
Body Pressure Rating	ANSI Class 250, up to 400 psi below 150°F	
Flow characteristic	modified equal percentage	
Leakage rate	ANSI Class VI	
Pipe connection	Internal thread NPT (female)	
Servicing	repack kits available	
Rangeability Sv	100:1	
Maximum differential pressure (water)	50 psi [345 kPa]	
Max Differential Pressure (Steam)	50 psi [345 kPa]	
Flow Pattern	2-way	
Controllable flow range	stem up - open A – AB	
Cv	1.3	
Maximum Inlet Pressure (Steam)	100 psi [690 kPa]	
Materials	Valve body	Bronze
	Valve plug	Stainless steel AISI 316
	Stem	316 stainless steel
	Stem seal	EPDM O-ring
	Seat	Stainless steel AISI 316
Suitable actuators	Non Fail-Safe	LVB(X)
	Spring	LF
	Electrical fail-safe	LVKB(X)


Safety notes



- **WARNING:** This product can expose you to lead which is known to the State of California to cause cancer and reproductive harm. For more information go to www.p65warnings.ca.gov
- The valve has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Only authorized specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.
- The valve does not contain any parts that can be replaced or repaired by the user.
- When determining the flow rate characteristic of controlled devices, the recognised directives must be observed.


Installation notes

Flow direction The direction of flow, specified by an arrow on the housing, is to be complied with, since otherwise the valve could become damaged.




Dimensions

Type	DN	Weight
G215S-F	15	2.1 lb [0.97 kg]



Dimensions



On/Off, Spring return, 120 V



5-year warranty



Technical data

Electrical data		
Nominal voltage	AC 120 V	
Nominal voltage frequency	50/60 Hz	
Nominal voltage range	AC 96...132 V	
Power consumption in operation	5.5 W	
Power consumption in rest position	3.5 W	
Transformer sizing	7.5 VA	
Auxiliary switch	1x SPDT, 1 mA...3 A (0.5 A inductive), DC 5 V...AC 250 V, adjustable 0...95°	
Switching capacity auxiliary switch	1 mA...3 A (0.5 A inductive), DC 5 V...AC 250 V	
Electrical Connection	(2) 18 GA appliance cables, 3 ft [1 m], with 1/2" NPT conduit connectors	
Overload Protection	electronic throughout 0...95° rotation	
Functional data		
Direction of motion motor	selectable with switch 0/1	
Direction of motion fail-safe	reversible with cw/ccw mounting	
Angle of rotation	90°	
Running Time (Motor)	75 s / 90°	
Running time fail-safe	<25 s @ -4...122°F [-20...50°C], <60 s @ -22°F [-30°C]	
Noise level, motor	50 dB(A)	
Noise level, fail-safe	62 dB(A)	
Position indication	Mechanical	
Safety data		
Degree of protection IEC/EN	IP54	
Degree of protection NEMA/UL	NEMA 2	
Enclosure	UL Enclosure Type 2	
Agency Listing	cULus acc. To UL 873 and CAN/CSA C22.2 No. 24-93	
Quality Standard	ISO 9001	
UL 2043 Compliant	Suitable for use in air plenums per Section 300.22(C) of the NEC and Section 602 of the IMC	
Ambient humidity	Max. 95% RH, non-condensing	
Ambient temperature	-22...122°F [-30...50°C]	
Storage temperature	-40...176°F [-40...80°C]	

Technical data

Safety data	Servicing	maintenance-free
Weight	Weight	□
Materials	Housing material	galvanized steel

Footnotes †Rated Impulse Voltage 800V, Type of action 1.AA, Control Pollution Degree 3

Electrical installation


 **INSTALLATION NOTES**

- Ⓐ Actuators with appliance cables are numbered.
- △1 Provide overload protection and disconnect as required.
- △11 Actuators may be connected in parallel if not mechanically linked. Power consumption and input impedance must be observed.
- △44 One built-in auxiliary switch (1x SPDT), for end position indication, interlock control, fan startup, etc.
- ⚡ Apply only AC line voltage or only UL-Class 2 voltage to the terminals of auxiliary switches. Mixed or combined operation of line voltage/safety extra low voltage is not allowed.
- ◆ Meets cULus requirements without the need of an electrical ground connection.
- ⚠ Warning! Live electrical components!

During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

Wiring diagrams

On/Off



Auxiliary Switches

