




5-year warranty



## Type overview

Type	DN
G250S-N	50

## Technical data

Functional data	Valve Size	2" [50]
Fluid	chilled or hot water, up to 60% glycol, steam	
Fluid Temp Range (water)	20...338°F [-7...170°C]	
Fluid Temp Range (steam)	32...338°F [0...170°C]	
Body Pressure Rating	ANSI Class 250, up to 400 psi below 150°F	
Flow characteristic	modified equal percentage	
Servicing	repack kits available	
Rangeability Sv	100:1	
Maximum differential pressure (water)	50 psi [345 kPa]	
Max Differential Pressure (Steam)	50 psi [345 kPa]	
Flow Pattern	2-way	
Leakage rate	ANSI Class VI	
Controllable flow range	stem up - open A - AB	
Cv	40	
Maximum Inlet Pressure (Steam)	100 psi [690 kPa]	
ANSI Class	250	
Body pressure rating note	up to 400 psi below 150°F	
Materials	Valve body	Bronze
	Valve plug	316 stainless steel
	Stem	316 stainless steel
	Stem seal	EPDM O-ring
	Seat	Stainless steel AISI 316
	Pipe connection	NPT female ends
Suitable actuators	Non-Spring	LV(B)(X)
	Electronic fail-safe	LVKB(X)


## Safety notes



- **WARNING:** This product can expose you to lead which is known to the State of California to cause cancer and reproductive harm. For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)
- The valve has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied during installation.
- The valve does not contain any parts that can be replaced or repaired by the user.
- When determining the flow rate characteristic of controlled devices, the recognised directives must be observed.


## Installation notes

**Flow direction** The direction of flow, specified by an arrow on the housing, is to be complied with, since otherwise the valve could become damaged.





## Dimensions

### Dimensional drawings



A	B	C	D	E	F
10.0" [254]	6.1" [156]	9.9" [252]	8.0" [203]	1.9" [48]	1.9" [48]







5-year warranty



## Technical data

Electrical data	
Nominal voltage	AC 24...240 V / DC 24...125 V
Nominal voltage frequency	50/60 Hz
Power consumption in operation	6 W
Power consumption in rest position	2.5 W
Transformer sizing	6 VA @ AC 24 V (class 2 power source), 6.5 VA @ AC 120 V, 9.5 VA @ AC 240 V
Auxiliary switch	2 x SPDT, 3 A resistive (0.5 A inductive) @ AC 250 V, one set at 10°, one adjustable 10...90°
Switching capacity auxiliary switch	3 A resistive (0.5 A inductive) @ AC 250 V
Electrical Connection	(2) 18 GA appliance cables with 1/2" conduit connectors, 3 ft [1 m],
Overload Protection	electronic throughout 0...95° rotation
Functional data	
Direction of motion motor	selectable by ccw/cw mounting
Direction of motion fail-safe	reversible with cw/ccw mounting
Manual override	5 mm hex crank (3/16" Allen), supplied
Angle of rotation	95°,
Running Time (Motor)	75 s
Running time fail-safe	<20 s @ -4...122°F [-20...50°C], <60 s @ -49°F [-45°C]
Noise level, motor	50 dB(A)
Noise level, fail-safe	62 dB(A)
Position indication	Mechanical
Safety data	
Degree of protection IEC/EN	IP54
Degree of protection NEMA/UL	NEMA 2 UL Enclosure Type 2
Agency Listing	UL 873 listed, CSA C22.2 No. 24 certified
Quality Standard	ISO 9001
Ambient temperature	-22...122°F [-30...50°C]
Storage temperature	-40...176°F [-40...80°C]
Ambient humidity	max. 95% r.H., non-condensing
Servicing	maintenance-free
Weight	
Weight	4.5 lb [2.0 kg]

## Safety notes



- PVC W'Shld for GV w/UGLK (AM)
- Battery Back Up System for SY(7~10)-110
- ZS-300 Mounting Bracket Set
- Weather shield - galvaneal 13x8x6" (LxWxD).
- Cable for ZTH US to diagnostic/programming socket.
- Cable for ZTH US to actuators w/o diagnostics socket.
- PC Tool computer programming interface, serial port.
- 3/4" shaft adaptor for ZS-300(-5).
- Battery Back Up System for SY(8~12)-110P
- 1/2" shaft adaptor, standard wthi ZS-300(-5).

## Electrical installation

## INSTALLATION NOTES

- A** Actuators with appliance cables are numbered.
- UP** Universal Power Supply (UP) models can be supplied with 24 VAC up to 240 VAC, or 24 VDC up to 125 VDC.
- 1** Provide overload protection and disconnect as required.
- 4** Two built-in auxiliary switches (2x SPDT), for end position indication, interlock control, fan startup, etc.
- ⚠** Apply only AC line voltage or only UL-Class 2 voltage to the terminals of auxiliary switches. Mixed or combined operation of line voltage/safety extra low voltage is not allowed.
- ◆** Meets cULus requirements without the need of an electrical ground connection.

**!** **Warning! Live Electrical Components!**

During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

