

ANSI-Flanged Globe Valves

- chilled or hot water, up to 60% glycol, steam
- ANSI Class 125, up to 175 psi below 150°F
- 125
- Cast iron ASTM A126 Class B





Type overview		
Туре		DN
G6150C		150
Technical data		
Functional data	Valve size [mm]	6" [150]
	Fluid	chilled or hot water, up to 60% glycol, steam
	Fluid Temp Range (water)	32338°F [0138°C]
	Fluid Temp Range (steam)	32280°F [0138°C]
	Body Pressure Rating	ANSI Class 125, up to 175 psi below 150°F
	Flow characteristic	equal percentage
	Leakage rate	ANSI Class III
	Pipe connection	Flange for use with ASME/ANSI class 125
	Servicing	repack/rebuild kits available
	Rangeability Sv	98:1
	Max Differential Pressure (Steam)	15 psi [103 kPa]
	Flow Pattern	2-way
	Controllable flow range	stem up - open A – AB
	Cv	344
	Maximum Inlet Pressure (Steam)	35 psi [241 kPa]
Materials	Valve body	Cast iron - ASTM A126 Class B
	Valve plug	brass
	Stem	stainless steel
	Stem seal	NLP EPDM (no lip packing)
	Seat	Stainless steel AISI 316
Suitable actuators	Non Fail-Safe	EVB(X)
	Spring	2*AFB(X)

AVKB(X)

Electrical fail-safe




Safety notes



- WARNING: This product can expose you to lead which is known to the State of California to cause cancer and reproductive harm. For more information go to www.p65warnings.ca.gov
- The valve has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Only authorized specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.
- The valve does not contain any parts that can be replaced or repaired by the user.
- When determining the flow rate characteristic of controlled devices, the recognised directives must be observed.


Dimensions

Туре	DN	Weight	
G6150C	150	150 lb [67 kg]	



EVB, EVX, RVB, RVX

Α	В	С	D	E	F	Number of Bolt Holes
16.1" [410]	17.8" [451]	27.9" [708]	19.4" [492]	5.6" [142]	5.6" [142]	8




2*AFB, 2*AFX

Α	В	С	D	E	F	Number of Bolt Holes
16.1" [410]	17.8" [451]	31.4" [797]	22.8" [578]	5.6" [142]	5.5" [140]	8



Dimensions





On/Off, Floating point, Electrical fail-safe, 24 V





5-year warranty



Inch	nical	data
ICUI	HILLA	uala

 ectri	

Nominal voltage	AC/DC 24 V
Nominal voltage frequency	50/60 Hz
Nominal voltage range	AC 19.228.8 V
Power consumption in operation	5 W
Power consumption in rest position	2 W
Transformer sizing	9.5 VA
Electrical Connection	18 GA plenum cable, 1 m, with 1/2" NPT conduit connector, degree of protection NEMA 2 / IP54
Overload Protection	electronic throughout full stroke
Electrical Protection	actuators are double insulated

Functional data

Actuating force motor	2000 N [450 lbf]
Position feedback U note	No Feedback
Bridging time (PF)	2 s
Pre-charging time	520 s
Direction of motion motor	selectable with switch
Direction of motion fail-safe	reversible with switch
Manual override	5 mm hex crank (3/16" Allen), supplied
Stroke	1.25" [32 mm]
Running Time (Motor)	90 s /
Running time motor note	constant, independent of load
Running time fail-safe	<35 s
Noise level, motor	60 dB(A)
Noise level, fail-safe	60 dB(A)
Position indication	Mechanical, with pointer
Power source UL	Class 2 Supply

Safety data

Power source UL	Class 2 Supply
Degree of protection IEC/EN	IP54
Degree of protection NEMA/UL	NEMA 2
Enclosure	UL Enclosure Type 2
Agency Listing	cULus acc. to UL60730-1A/-2-14, CAN/CSA E60730-1:02, CE acc. to 2014/30/EU and 2014/35/EU
Quality Standard	ISO 9001
Ambient humidity	Max. 95% RH, non-condensing
Ambient temperature	-22122°F [-3050°C]
Storage temperature	-40176°F [-4080°C]



Technical data

Safety data	Servicing	maintenance-free
Weight	Weight	0
Materials	Housing material	Die cast aluminium and plastic casing

Footnotes

† Use flexible metal conduit. Push the listed conduit fitting device over the actuator's cable to butt against the enclosure. Screw in conduit connector. Jacket the actuators input wiring with listed flexible conduit. Properly terminate the conduit in a suitable junction box. Rated impulse Voltage 800V. Type of action 1. Control pollution degree 3.

Electrical installation



INSTALLATION NOTES

Meets cULus requirements without the need of an electrical ground connection.

Provide overload protection and disconnect as required.

Actuators may be connected in parallel. Power consumption and input impedance must be observed.

Control signal may be pulsed from either the Hot (Source) or Common (Sink) 24 V line. Actuators may be connected in parallel if not mechanically linked. Power consumption and input impedance must be observed.


Actuators with plenum cable do not have numbers; use color codes instead.

Warning! Live electrical components!

During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

Wiring diagrams

On/Off





Electrical installation

Wiring diagrams

