



5-year warranty

## Type overview

Type	DN
G7150-250	150

## Technical data

Functional data	
Valve size [mm]	6" [150]
Fluid	chilled or hot water, up to 60% glycol
Fluid Temp Range (water)	32...350°F [0...176°C]
Body Pressure Rating	ANSI Class 250, up to 280 psi below 350°F
Flow characteristic	linear
Servicing	repack/rebuild kits available
Rangeability Sv	50:1
Flow Pattern	3-way Mixing
Leakage rate	ANSI Class III
Controllable flow range	stem up - open B – AB
Cv	340
Materials	
Valve body	Cast iron - ASTM A126 Class B
Valve plug	bronze
Stem	stainless steel
Stem seal	NLP EPDM (no lip packing)
Seat	Stainless steel AISI 316
Pipe connection	250 lb flanged
Suitable actuators	
Non-Spring	RVB(X) EVB(X)
Electrical fail-safe	(2*GKB(X))

## Safety notes




- WARNING: This product can expose you to lead which is known to the State of California to cause cancer and reproductive harm. For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)
- The valve has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Only authorized specialists may carry out installation. All applicable legal or institutional installation regulations must be complied during installation.
- The valve does not contain any parts that can be replaced or repaired by the user.
- When determining the flow rate characteristic of controlled devices, the recognised directives must be observed.

## Dimensions


Type	DN	Weight
G7150-250	150	286.6 lb [130 kg]

EVB, EVX, RVB, RVX



A	B	C	D	E	F	Number of Bolt Holes
18.6" [473]	18.6" [473]	30.4" [772]	19.4" [492]	6.3" [160]	6.3" [160]	12

2\*GMB, 2\*GMX, 2\*GKB, 2\*GKX



A	B	C	D	E	F	Number of Bolt Holes
16.5" [420]	18.6" [473]	30.4" [772]	19.4" [492]	5.5" [140]	6.3" [160]	12



5-year warranty

**Technical data**

<b>Electrical data</b>	
Nominal voltage	AC/DC 24 V
Nominal voltage frequency	50/60 Hz
Power consumption in operation	6 W
Power consumption in rest position	1.5 W
Transformer sizing	11 VA (class 2 power source)
Electrical Connection	18 GA plenum cable, 3 ft [1 m], with 1/2" conduit connector, degree of protection NEMA 2 / IP54
Overload Protection	electronic throughout full stroke
Electrical Protection	actuators are double insulated
<b>Functional data</b>	
Actuating force motor	4500 N [1010 lbf]
Operating range Y	2...10 V
Operating range Y note	4...20 mA w/ ZG-R01 (500 Ω, 1/4 W resistor)
Input Impedance	100 kΩ for 2...10 V (0.1 mA), 500 Ω for 4...20 mA, 1500 Ω for On/Off
Operating range Y variable	Start point 0.5...30 V End point 2.5...32 V
Options positioning signal	variable (VDC, on/off, floating point)
Position feedback U	2...10 V
Position feedback U note	Max. 0.5 mA
Position feedback U variable	VDC variable
Direction of motion motor	selectable with switch
Manual override	5 mm hex crank (3/16" Allen), supplied
Stroke	2" [50 mm]
Running Time (Motor)	90 s /
Running time motor note	constant, independent of load
Noise level, motor	65 dB(A)
Position indication	Mechanically, with pointer
<b>Safety data</b>	
Degree of protection IEC/EN	IP54
Degree of protection NEMA/UL	NEMA 2
Enclosure	UL Enclosure Type 2
Agency Listing	cULus acc. to UL60730-1A-2-14, CAN/CSA E60730-1:02, CE acc. to 2014/30/EU and 2014/35/EU
Quality Standard	ISO 9001
Ambient temperature	-22...122°F [-30...50°C]
Storage temperature	-40...176°F [-40...80°C]
Ambient humidity	Max. 95% RH, non-condensing
Servicing	maintenance-free

Materials	Housing material	Die cast aluminium and plastic casing
-----------	------------------	---------------------------------------

Footnotes	† Use flexible metal conduit. Push the listed conduit fitting device over the actuator's cable to butt against the enclosure. Screw in conduit connector. Jacket the actuators input wiring with listed flexible conduit. Properly terminate the conduit in a suitable junction box. Rated impulse Voltage 800V. Type of action 1. Control pollution degree 3.
-----------	--

## Accessories

Gateways	Description	Type
	Gateway MP to BACnet MS/TP	UK24BAC
Electrical accessories	Gateway MP to Modbus RTU	UK24MOD
	Gateway MP to LonWorks	UK24LON
Electrical accessories	Description	Type
	Battery backup system, for non-spring return models	NSV24 US
Service tools	Battery, 12 V, 1.2 Ah (two required)	NSV-BAT
	Belimo PC-Tool, Software for adjustments and diagnostics	MFT-P
	Auxiliary switch 2 x SPDT for NG GV Actuators	S2A-GV
	Service Tool, with ZIP-USB function, for programmable and communicative Belimo actuators, VAV controller and HVAC performance devices	ZTH US
	Description	Type
Service tools	Connection cable 10 ft [3 m], A: RJ11 6/4 ZTH EU, B: 3-pin Weidmüller and supply connection	ZK4-GEN
	Service Tool, with ZIP-USB function, for programmable and communicative Belimo actuators, VAV controller and HVAC performance devices	ZTH US


## Electrical installation

### INSTALLATION NOTES


-  Actuators may be connected in parallel. Power consumption and input impedance must be observed.
-  Actuators may also be powered by DC 24 V.
-  A 500  $\Omega$  resistor (ZG-R01) converts the 4...20 mA control signal to 2...10 V.
-  Control signal may be pulsed from either the Hot (Source) or Common (Sink) 24 V line.
-  For triac sink the common connection from the actuator must be connected to the hot connection of the controller. Contact closures A & B also can be triacs. A & B should both be closed for the triac source and open for triac sink.
-  Actuators with plenum cable do not have numbers; use color codes instead.
-  Meets cULus requirements without the need of an electrical ground connection.
-  **Warning! Live electrical components!**  
During installation, testing, servicing and troubleshooting of this product, it may be necessary to work with live electrical components. Have a qualified licensed electrician or other individual who has been properly trained in handling live electrical components perform these tasks. Failure to follow all electrical safety precautions when exposed to live electrical components could result in death or serious injury.

## Wiring diagrams


On/Off



## Floating Point



VDC / 4 to 20 mA



## Override Control Min, Mid, Max Positions

