



2-year warranty

## Type overview

| Type        | DN |
|-------------|----|
| ZONE215S-10 | 15 |

## Technical data

|                    |                          |                                        |
|--------------------|--------------------------|----------------------------------------|
| Functional data    | Valve size [mm]          | 0.5" [15]                              |
|                    | Fluid                    | chilled or hot water, up to 50% glycol |
|                    | Fluid Temp Range (water) | 32...212°F [0...100°C]                 |
|                    | Body Pressure Rating     | 300 psi                                |
|                    | Close-off pressure Δps   | 75 psi                                 |
|                    | Flow characteristic      | on/off                                 |
|                    | Flow Pattern             | 2-way                                  |
|                    | Leakage rate             | ANSI Class III 0.1%                    |
|                    | Cv                       | 1                                      |
| Materials          | Valve body               | forged brass                           |
|                    | Housing seal             | EPDM                                   |
|                    | Spindle                  | stainless steel                        |
|                    | Seat                     | EPDM                                   |
|                    | Pipe connection          | sweat                                  |
| Suitable actuators | Spring                   | ZONE                                   |

## Product features

**Application** This valve is typically used on fan coil units, baseboards or other hydronic applications where fail safe operation on 2-wire control is required. This valve is suitable for use in a hydronic system with variable or constant flow.

This valve is designed to fit in compact areas where on/off or control is required using 24 VAC or 120 VAC.

## Dimensions

| Type        | DN |
|-------------|----|
| ZONE215S-10 | 15 |



| A          | B         | C         | D          | E         | F         |
|------------|-----------|-----------|------------|-----------|-----------|
| 4.0" [102] | 2.8" [70] | 3.5" [89] | 4.3" [110] | 1.2" [30] | 1.2" [31] |



2-year warranty



## Technical data

|                 |                                |                             |
|-----------------|--------------------------------|-----------------------------|
| Electrical data | Nominal voltage                | AC 230 V                    |
|                 | Nominal voltage frequency      | 50/60 Hz                    |
|                 | Power consumption in operation | 6.5 W                       |
|                 | Transformer sizing             | 7 VA (class 2 power source) |
|                 | Electrical Connection          | 6" wire leads               |
| Functional data | Angle of rotation              | 90°                         |
|                 | Running time fail-safe         | <5 s                        |
|                 | Noise level, motor             | 35 dB(A)                    |
|                 | Noise level, fail-safe         | 35 dB(A)                    |
| Safety data     | Degree of protection IEC/EN    | IP20                        |
|                 | Degree of protection NEMA/UL   | NEMA 1                      |
|                 | Enclosure                      | UL Enclosure Type 1         |
|                 | Agency Listing                 | CE, cULus                   |
|                 | Quality Standard               | ISO 9001                    |
|                 | Ambient temperature            | 32...104 [0...40°C]         |
|                 | Storage temperature            | -40...176°F [-40...80°C]    |
|                 | Ambient humidity               | Max. 95% RH, non-condensing |
| Materials       | Servicing                      | maintenance-free            |
|                 | Housing material               | galvanized steel            |

## Electrical installation

### ✂ INSTALLATION NOTES

- ◆ Meets cULus requirements without the need of an electrical ground connection.
- ⚠ One built-in auxiliary switch, 1x SPST 0.4A @ 24 VAC (resistive and inductive loads).

### Wiring diagrams

Built-in Auxiliary Switch (optional) (only on -S models)

