

Air differential pressure sensor dual with two additional inputs

Differential pressure transmitter with two independent measuring systems. With 8 selectable ranges each and Modbus functionality. Two additional inputs are available to which a potential-free contact or an NTC10k resistance sensor can be connected. The values at the additional inputs can be read out via Modbus. For monitoring over-, under- or the differential pressure of air and other non-flammable and non-aggressive gases. Typical application in HVAC systems for monitoring air filters, fans V-belts as well as the use in pressure differential systems. IP65 / NEMA 4X rated housing.



## Type Overview

Type	Measuring range [Pa]	Communication	Output signal active pressure	Output signal active volumetric flow	Burst pressure
22ADP-154H	-100...2500	Modbus RTU	0...5 V, 0...10 V	0...5 V, 0...10 V	40 kPa

## Technical data

<b>Electrical data</b>	Nominal voltage	AC/DC 24 V
	Nominal voltage range	AC 19...29 V / DC 15...35 V
	Power consumption AC	4.3 VA
	Power consumption DC	2.3 W
	Electrical connection	Pluggable spring loaded terminal block max. 2.5 mm <sup>2</sup>
	Cable entry	Cable gland with strain relief 2x ø6 mm
<b>Data bus communication</b>	Communication	Modbus RTU
	Number of nodes	Modbus see interface description
<b>Functional data</b>	Medium	Air
	Multirange	8 measuring ranges selectable
	Voltage output	2 x 0...5 V, 0...10 V, min. resistance 10 kΩ
	Output signal active note	Output 0...5/10 V selectable with switch
	Typical response time	Adjustable 0.8 s or 4.0 s
	Notes	Additional inputs Two inputs (IN1 and IN2) for connecting a potential-free contact (max. 0.3 mA @ 3.3 V) or an NTC10k resistance sensor (beta value sensor adjustable via Modbus register).
<b>Measuring data</b>	Measured values	Differential pressure Volumetric flow
	Measuring fluid	Air and non-aggressive gases
<b>Specification Flow</b>	Measuring range volumetric flow	Adjustable via Modbus Default setting: 0...750'000 m <sup>3</sup> /h Selectable units: m <sup>3</sup> /h, m <sup>3</sup> /s, cfm
<b>Specification Pressure</b>	Sensing element technology	Piezo measuring element
	Measuring range	-100...2500 Pa

## Technical data

Specification	Pressure	Measuring range pressure settings	*del*	Setting	Range	Range [inch WC]	Factory setting
			S0		0...2500	0...10	✓
			S1		0...2000	0...8	
			S2		0...1500	0...6	
			S3		0...1000	0...4	
			S4		0...500	0...2	
			S5		0...250	0...1	
			S6		0...100	0...0.4	
			S7		-100...100	-0.4...0.4	
Accuracy		Deviation compared to the reference device measuring range ≤500 Pa: ±5 Pa measuring range >500 Pa: ±10 Pa					
Long term stability		±2.5% FSO (Full Scale Output) / 4 yr.					
Safety data		Protection class IEC/EN III, Safety Extra-Low Voltage (SELV)					
Power source UL		Class 2 Supply					
Degree of protection IEC/EN		IP65					
Degree of protection NEMA/UL		NEMA 4X					
Housing		UL Enclosure Type 4X					
EU Conformity		CE Marking					
Certification IEC/EN		IEC/EN 60730-1 and IEC/EN 60730-2-6					
Quality Standard		ISO 9001					
UL Approval		cULus acc. to UL60730-1A/-2-6, CAN/CSA E60730-1					
Type of action		Type 1					
Rated impulse voltage supply		0.8 kV					
Pollution degree		3					
Ambient humidity		Max. 95% RH, non-condensing					
Ambient temperature		-10...50°C [14...122°F]					
Fluid temperature		-10...50°C [15...120°F]					
Materials		Housing Cover: PC, orange Bottom: PC, orange Seal: NBR70, black UV resistant					
Cable gland		PA6, black					

## Safety notes



This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application. Unauthorised modifications are prohibited. The product must not be used in relation with any equipment that in case of a failure may threaten humans, animals or assets.

Ensure all power is disconnected before installing. Do not connect to live/operating equipment.

Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.


The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

## Remarks

<b>Manual zero-point calibration</b>	<p>After initial commissioning</p> <p>To carry out the zero-point calibration, the device must be connected to the power supply at least 15 minutes beforehand.</p> <p>Calibration interval</p> <p>≤250 Pa 3 months</p> <p>≤500 Pa 6 months</p> <p>&gt;500 Pa 12 months</p> <p>Procedure</p> <ul style="list-style-type: none"> <li>Release both tube connectors from the pressure ports + and -</li> <li>(Carry out the manual zero-point calibration even if the display shows 0.)</li> <li>Press the button "Manual zero-point calibration" until the LED lights permanently</li> <li>Wait until the LED flashes again and reinstall the tube connectors to the pressure ports (pay attention to + and -)</li> </ul>
--------------------------------------	---

## Indicators

<b>Indicators</b>	Depending on the device and the number of measured values, the display automatically scales. Parameters, such as the fading in/out of measured values, brightness and traffic light function, are changed via the app or bus system. During the boot process, the software and hardware versions are displayed.
-------------------	---



- ① Fault / sensor failure
- ② Service / visual inspection due
- ③ TLF (traffic light function) active (thresholds for display colour changes)
- ④ Radio active (not available)
- ⑤ Status bar
- ⑥ Measured value (\* appears when TLF function is activated for this value)
- ⑦ Unit of measure
- ⑧ Measured value

## Parts included

	Description	Type
Mounting plate L housing		A-22D-A10
Duct connector kit, Plastic, PVC tube 2 m, 2x duct connector (plastic) for 22ADP-..		A-22AP-A08
Cable Gland with strain relief ø6...8 mm		
Dowels		
Screws		

## Accessories


Optional accessories	Description	Type
Duct connector, Metal, L 40 mm, Tube connection 5 mm		A-22AP-A02
Duct connector, Metal, L 100 mm, Tube connection 5 mm		A-22AP-A04
Connection adapter flex conduit, M20x1.5, for cable gland 1x 6 mm, Multipack 10 pcs.		A-22G-A01.1
Connection adapter flex conduit, M20, for cable gland 2x 6 mm, Multipack 10 pcs.		A-22G-A02.1
Tools	Description	Type
Belimo Duct Sensor Assistant App		Belimo Duct Sensor Assistant App

## Accessories

Description	Type
Bluetooth dongle for Belimo Duct Sensor Assistant App	A-22G-A05
* Bluetooth dongle A-22G-A05	
Certified and available in North America, European Union, EFTA States and UK.	

## Service

<b>Tools connection</b>	<p>This sensor can be operated and configured using the Belimo Duct Sensor Assistant App. When using the Belimo Duct Sensor Assistant App, the bluetooth dongle is required to enable communication between the app and the Belimo sensor. For standard operation and configuration of the sensor, the bluetooth dongle and the Belimo Duct Sensor Assistant App are not needed. The sensor will arrive pre-configured with the factory default settings shown above.</p> <p>Requirement:</p> <ul style="list-style-type: none"><li>- Bluetooth dongle (Belimo Part No: A-22G-A05)</li><li>- Bluetooth-capable smartphone</li><li>- Belimo Duct Sensor Assistant App (Google Play &amp; Apple App Store)</li></ul> <p>Procedure:</p> <ul style="list-style-type: none"><li>- Plug the Bluetooth dongle into the sensor via the Micro-USB connector or by means of the interface PCB</li><li>- Connect Bluetooth-capable smartphone with Bluetooth dongle</li><li>- Select configuration in the Belimo Duct Sensor Assistant App</li></ul>
-------------------------	---



## Wiring diagram



## Supply from isolating transformer.

The wiring of Modbus RTU (RS-485) is to be carried out in accordance with applicable regulations ([www.modbus.org](http://www.modbus.org)). The device has switchable resistors for bus termination.

Modbus / BACnet: Supply and communication are not galvanically isolated. Connect earth signal of the devices with one another.

## Wiring diagram

Manual zero-point calibration ①

Red: Error ②

Yellow: Tx ③

Yellow: Rx ④

Status LED ⑤ and ⑥

Slow flashing (0.5 Hz): Ok


Fast flashing (4 Hz): Error

Factory setting \*

Pressure unit P

Response time T

Output signal U



## Detailed documentation

The separate document Sensor Modbus-Register informs about Modbus register, addressing, parity and bus termination (DIP1: address, DIP2: baud rate, parity, bus termination)

In addition to the information on the bus, the following analog outputs are available:

AOU1: differential pressure 1

AOU2: differential pressure 2

If required, the outputs AOU1 and AOU2 can be changed to volumetric flow via bus system.


The volumetric flow is calculated from the differential pressure, the k-factor and the height.

Factory setting for the k-factor is 1.00 and for the height 330 metres above sea level.


The values of the k-factor and the height can be changed via bus system.

The inputs IN1 and IN2 are read out via bus system, further information in the bus system document.

## Wiring RS-485 Modbus RTU



## Dimensions



## Type

22ADP-154H

## Weight

0.47 kg

## Further documentation

- Modbus Interface description
- Installation instructions