

## Actuator for smoke control dampers 90°

- Torque motor 40 Nm
- Nominal voltage AC 230 V
- Control Open/close
- Mechanical interface Form fit 14x14 mm, continuous hollow shaft



Picture may differ from product

## Technical data

Electrical data	Nominal voltage	AC 230 V
	Nominal voltage frequency	50/60 Hz
	Nominal voltage range	AC 198...264 V
	Switching thresholds min. ON voltage	AC 198 V
	Switching thresholds max. OFF voltage	AC 100 V
	Power consumption in operation	8 W
	Power consumption in rest position	0.5 W
	Power consumption for wire sizing	15 VA
	Inrush current (Imax)	7.9 A @ 5 ms
	Auxiliary switch	2x SPDT
	Switching capacity auxiliary switch	1 mA...6 A (3 A inductive), DC 5 V...AC 250 V
	Switching points auxiliary switch	3° / 87°
	Tolerance	±2°
	Connection supply / control	Cable 1 m, 3x 0.75 mm <sup>2</sup> , halogen-free
	Connection auxiliary switch	Cable 1 m, 6x 0.75 mm <sup>2</sup> , halogen-free
Functional data	Torque motor	40 Nm
	Inhibiting torque dynamic	40 Nm
	Inhibiting torque static (voltage-free)	50 Nm
	Direction of motion motor	selectable by mounting L/R
	Manual override	with hand crank
	Angle of rotation	Max. 100°
	Angle of rotation note	Including 5° mechanical overrun at both sides
	Running time motor	<60 s / 90°
	Sound power level, motor	62 dB(A)
	Mechanical interface	Form fit 14x14 mm, continuous hollow shaft
	Position indication	Mechanical, with pointer
	Service life	Min. 10'000 cycles
Safety data	Protection class IEC/EN	II, reinforced insulation
	Protection class auxiliary switch IEC/EN	II, reinforced insulation
	Degree of protection IEC/EN	IP54
	EMC	CE according to 2014/30/EU
	Low voltage directive	CE according to 2014/35/EU
	Certification IEC/EN	IEC/EN 60730-1 and IEC/EN 60730-2-14
	Type of action	Type 1.B
	Rated impulse voltage supply / control	4 kV

<b>Safety data</b>	Rated impulse voltage auxiliary switch	2.5 kV
Pollution degree		3
Ambient humidity		Max. 95% RH, non-condensing
Ambient temperature		-30...50°C [-22...122°F]
Storage temperature		-40...80°C [-40...176°F]
Servicing		maintenance-free
<b>Weight</b>	<b>Weight</b>	2.6 kg

## Safety notes



- The device must not be used outside the specified field of application, especially not in aircraft or in any other airborne means of transport.
- Caution: Mains voltage!
- The actuator is adapted to and installed on the smoke control damper by the damper manufacturer. For this reason, the actuator is only supplied direct to safety damper manufacturers. The manufacturer then bears full responsibility for the proper functioning of the damper.
- The two switches integrated in the actuator are to be operated either on mains voltage or on safety extra-low voltage. The combination mains voltage/safety extra-low voltage is not permitted.
- Because of the fact that very high torques are applied to the damper shaft, the use of St50 (as a minimum) is recommended.
- The device may only be opened at the manufacturer's site. It does not contain any parts that can be replaced or repaired by the user.
- The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

## Product features

<b>Operating mode</b>	2-wire open/close control. The actuator is overload-proof and can thus remain energised even at the end stops.
<b>Manual override</b>	The hand crank included in the shipment can be used for manual operation of the actuator.
<b>Signalling</b>	Two microswitches with fixed settings are installed in the actuator for indicating the damper end positions. It should be noted with this application however that the contacts can no longer be used in the milliamperc range after larger currents have been applied to them, even if this has taken place only once. The position of the damper blade can be read off on a mechanical position indicator.
<b>Standards / Regulations</b>	The design of the actuator is based on the specific requirements from the European standards: <ul style="list-style-type: none"> <li>• EN 12101-8: Smoke and heat control systems - Part 8: Smoke control dampers</li> <li>• EN 1366-10: Fire resistance tests for service installations - Part 10: Smoke control dampers</li> <li>• EN 13501-4: Fire classification of construction products and building elements - Part 4: Classification using data from fire resistance tests on components of smoke control systems</li> </ul>

## Parts included

Hand crank  
Pointer  
Protective bag

## Accessories

Mechanical accessories	Description	Type
	Hand crank 40 mm	ZK1-B
	Hand crank 70 mm	ZK2-B
	Protective bag with wire, Multipack 100 pcs.	ZSD-B.1

## Electrical installation



## Caution: Mains voltage!


Parallel connection of other actuators possible. Observe the performance data and the switching thresholds.

Combination of mains voltage and safety extra-low voltage not permitted at the two auxiliary switches.


## Wire colours:

1 = blue  
2 = white  
3 = white  
S1 = white  
S2 = white  
S3 = white  
S4 = white  
S5 = white  
S6 = white

AC 230 V, open/close



Auxiliary switch



## Dimensions

