

## Liquid differential pressure sensor

Active sensor (0...10 V) for differential pressure measurement in HVAC systems. The sensor is suitable for liquids, refrigerants or non-aggressive gases. The housing is made of stainless steel and is IP65 / NEMA 4 rated. Optional stainless steel or brass pipe connection adaptors also available.



## Type Overview

Type	Measuring range [bar]	Output signal active pressure	Overpressure	Negative overpressure	Burst pressure
22WDP-111	0...1	0...10 V	6 bar	-1 bar	21 bar
22WDP-112	0...2.5	0...10 V	6 bar	-1 bar	21 bar
22WDP-114	0...4	0...10 V	16 bar	-1 bar	21 bar
22WDP-115	0...6	0...10 V	16 bar	-1 bar	21 bar

Measuring range: The sensor can measure differential pressure (dp) within this range.

The maximum operating pressure (relative pressure to atmosphere prel) can be higher. For further information, please refer to "Product features".

## Technical data

<b>Electrical data</b>	Nominal voltage	AC/DC 24 V
	Nominal voltage range	AC 21.6...26.4 V / DC 13.5...26.4 V
	Power consumption AC	0.9 VA
	Power consumption DC	0.37 W
	Electrical connection	Connector plug for wire 0.5...1.5 mm <sup>2</sup>
	Cable entry	Angle plug according to DIN 43650, construction A
<b>Functional data</b>	Medium	Water Water-glycol mixture Steam
	Voltage output	1 x 0...10 V, min. resistance 2 kΩ
	Mechanical connection	pressure connector: G 1/4"
	Mounting	Installation location unrestricted
	Typical response time	100 ms
	Measured values	Differential pressure
<b>Specification Pressure</b>	Accuracy	±1% of measuring range @ -5...75°C [23...167°F]
	Long term stability	±2.5% / 10 yr.
<b>Safety data</b>	Protection class IEC/EN	III, Protective Extra-Low Voltage (PELV)
	Power source UL	Class 2 Supply
	Degree of protection IEC/EN	IP65
	Degree of protection NEMA/UL	NEMA 4
	EU Conformity	CE Marking
	Certification IEC/EN	IEC/EN 60730-1
	Quality Standard	ISO 9001
	Burst pressure	21 bar
	Ambient humidity	Max. 95% RH, non-condensing

## Technical data

<b>Safety data</b>	Ambient temperature	-10...50°C [14...122°F]
	Fluid temperature	-10...80°C [15...175°F]
	Fluid temperature note	At a fluid temperature of <2°C [<36°F], frost protection must be guaranteed steam inlet @ max. 100 kPa [15 psi]
<b>Materials</b>	Housing	Bottom: Stainless steel 1.4305 Top Cover: Die cast aluminium
	Housing seal	EPDM
	Fluid wetted parts	Stainless steel 1.4301, Ceramic

## Safety notes



This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application. Unauthorised modifications are prohibited. The product must not be used in relation with any equipment that in case of a failure may threaten humans, animals or assets.

Ensure all power is disconnected before installing. Do not connect to live/operating equipment.

Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.

The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

## Product Features


<b>Application</b>	The device is designed with an internal membrane that directly measures the differential pressure of the medium applied to each side of the sensing element. The operating pressure prel can be higher than the measuring range dp if it is guaranteed that the differential pressure stays within the measuring range.  Differential pressure <= measuring range (dp) Operating pressure < burst pressure (prel)  Measuring range (dp) The sensor can measure differential pressure (dp) within this range.  Overpressure (dp) Maximum differential pressure (dp) that the device can withstand without permanent damage. No measurement is possible within the overpressure range.  Negative Overpressure (dp) Maximum negative differential pressure (dp) that the device can withstand without permanent damage.  Burst pressure (prel) Maximum relative pressure (prel) up to which the device housing is tight. If this pressure is exceeded, the sensor will leak or burst.
--------------------	---

⚠ Operation possible, but overpressure must be considered during installation and operation.

OP: Operating pressure (prel) in bar – high pressure side

dp: Differential pressure in bar


AP: Ambient pressure




## Accessories

Optional accessories	Description	Type
	Pipe connector, Brass, Pipe 6 mm to G 1/4" (external thread), Set of 2 pcs.	A-22WP-A04
	Pipe connector, Stainless steel, Pipe 6 mm to G 1/4" (external thread), Set of 2 pcs.	A-22WP-A06
	Pipe connector, Brass, Pipe 8 mm to G 1/4" (external thread), Set of 2 pcs.	A-22WP-A08
	Pipe connector, Stainless steel, Pipe 8 mm to G 1/4" (external thread), Set of 2 pcs.	A-22WP-A10
	Mounting bracket for 22WDP-.., Metal	A-22WP-A11
	Pipe connector, Brass, Pipe 6 mm to G 1/4" (external thread)	EXT-BC1414
Electrical accessories	Description	Type
	Connecting cable 1.5 m for 22WP-.. / 22WDP-..	EXT-MR-249184
	Connecting cable 5 m for 22WP-.. / 22WDP-..	EXT-MR-249185

## Wiring diagram



## Dimensions



Type	Weight
22WDP-111	0.55 kg
22WDP-112	0.55 kg
22WDP-114	0.55 kg
22WDP-115	0.55 kg

## Further documentation

- Installation instructions