

Rotary actuator fail-safe for adjusting dampers in technical building installations

- Air damper size up to approx. 0.8 m²
- Torque motor 4 Nm
- Nominal voltage AC/DC 24 V
- Control Open/close



Picture may differ from product

Technical data

Electrical data	
	Nominal voltage AC/DC 24 V
	Nominal voltage frequency 50/60 Hz
	Nominal voltage range AC 19.2...28.8 V / DC 21.6...28.8 V
	Power consumption in operation 5 W
	Power consumption in rest position 2.5 W
	Power consumption for wire sizing 7 VA
	Inrush current (Imax) 5.8 A @ 5 ms
	Connection supply / control Cable 1 m, 2x 0.75 mm ²
	Parallel operation Yes (note the performance data)
Functional data	
	Torque motor 4 Nm
	Torque fail-safe 4 Nm
	Direction of motion motor selectable by mounting L/R
	Direction of motion fail-safe selectable by mounting L/R
	Manual override No
	Angle of rotation Max. 95°
	Angle of rotation note Adjustable 37...100% with integrated mechanical limitation
	Running time motor 75 s / 90°
	Running time fail-safe <20 s @ -20...50°C, <60 s @ -30°C
	Sound power level, motor 50 dB(A)
	Mechanical interface Universal shaft clamp 8...16 mm
	Position indication Mechanical
	Service life Min. 60'000 fail-safe positions
Safety data	
	Protection class IEC/EN III, Safety Extra-Low Voltage (SELV)
	Degree of protection IEC/EN IP54
	EMC CE according to 2014/30/EU
	Low voltage directive CE according to 2014/35/EU
	Certification IEC/EN IEC/EN 60730-1 and IEC/EN 60730-2-14
	Hygiene test According to VDI 6022 Part 1 / SWKI VA 104-01, cleanable and disinfectable, low emission
	Type of action Type 1.B
	Rated impulse voltage supply / control 0.8 kV
	Pollution degree 3
	Ambient humidity Max. 95% RH, non-condensing

Safety data	Ambient temperature	-30...50°C [-22...122°F]
	Storage temperature	-40...80°C [-40...176°F]
	Servicing	maintenance-free
Weight	Weight	1.4 kg

Safety notes



- This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Outdoor application: only possible in case that no (sea) water, snow, ice, insolation or aggressive gases interfere directly with the device and that it is ensured that the ambient conditions remain within the thresholds according to the data sheet at any time.
- Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.
- The device may only be opened at the manufacturer's site. It does not contain any parts that can be replaced or repaired by the user.
- Cables must not be removed from the device.
- To calculate the torque required, the specifications supplied by the damper manufacturers concerning the cross-section and the design, as well as the installation situation and the ventilation conditions must be observed.
- The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

Product features

Operating mode The actuator moves the damper to the operating position at the same time as tensioning the return spring. The damper is turned back to the safety position by spring energy when the supply voltage is interrupted.

Simple direct mounting Simple direct mounting on the damper shaft with a universal shaft clamp, supplied with an anti-rotation mechanism to prevent the actuator from rotating.

Adjustable angle of rotation Adjustable angle of rotation with mechanical end stops.

High functional reliability The actuator is overload protected, requires no limit switches and automatically stops when the end stop is reached.

Accessories

Electrical accessories	Description	Type
	Auxiliary switch 2x SPDT	S2A-F
	Feedback potentiometer 1 kΩ	P1000A-F
Mechanical accessories	Description	Type
	Shaft extension 170 mm Ø10 mm for damper shaft Ø6...16 mm	AV6-20
	Shaft clamp reversible, clamping range Ø16...20 mm	K6-1
	Ball joint suitable for damper crank arm KH8 / KH10	KG10A
	Ball joint suitable for damper crank arm KH8	KG8
	Damper crank arm Slot width 8.2 mm, clamping range Ø10...18 mm	KH8
	Actuator arm, clamping range Ø8...16 mm, Slot width 8.2 mm	KH-LF
	Angle of rotation limiter, with end stop	ZDB-LF
	Form fit adapter 8x8 mm	ZF8-LF
	Mounting kit for linkage operation for flat installation	ZG-LF1
	Mounting kit for linkage operation for side installation Slot width 6.2 mm	ZG-LF3
	Anti-rotation mechanism 180 mm, Multipack 20 pcs.	Z-ARS180L


Electrical installation

**Supply from isolating transformer.****Parallel connection of other actuators possible. Observe the performance data.****Wire colours:**

1 = black

2 = red


AC/DC 24 V, open/close



Dimensions

Spindle length

	Min. 84
	Min. 20 mm [0.75"]

**Clamping range**

8...16	8...16

