

Linear actuator for adjusting dampers and slide valves in technical building installations

- Air damper size up to approx. 1 m<sup>2</sup>
- Actuating force 150 N
- Nominal voltage AC/DC 24 V
- Control Open/close, 3-point
- Length of Stroke Max. 300 mm, adjustable in 20 mm increments



Picture may differ from product

## Technical data

Electrical data	
	Nominal voltage
	AC/DC 24 V
	Nominal voltage frequency
	50/60 Hz
	Nominal voltage range
	AC 19.2...28.8 V / DC 19.2...28.8 V
	Power consumption in operation
	1.5 W
	Power consumption in rest position
	0.5 W
	Power consumption for wire sizing
	3 VA
	Connection supply / control
	Cable 1 m, 3x 0.75 mm <sup>2</sup>
	Parallel operation
	Yes (note the performance data)
Functional data	
	Actuating force motor
	150 N
	Direction of motion motor
	selectable with switch 0 (extended) / 1 (retracted)
	Manual override
	with push-button, can be locked
	Stroke
	300 mm
	Length of Stroke
	Max. 300 mm, adjustable in 20 mm increments
	Stroke limitation
	can be limited on both sides with mechanical end stops
	Running time motor
	150 s / 100 mm
	Sound power level, motor
	45 dB(A)
Safety data	
	Protection class IEC/EN
	III, Safety Extra-Low Voltage (SELV)
	Power source UL
	Class 2 Supply
	Degree of protection IEC/EN
	IP54
	Degree of protection NEMA/UL
	NEMA 2
	Housing
	UL Enclosure Type 2
	EMC
	CE according to 2014/30/EU
	Certification IEC/EN
	IEC/EN 60730-1 and IEC/EN 60730-2-14
	UL Approval
	cULus according to UL60730-1A, UL60730-2-14 and CAN/CSA E60730-1
	The UL marking on the actuator depends on the production site, the device is UL-compliant in any case
	Hygiene test
	According to VDI 6022 Part 1 / SWKI VA 104-01, cleanable and disinfectable, low emission
	Type of action
	Type 1
	Rated impulse voltage supply / control
	0.8 kV
	Pollution degree
	3
	Ambient humidity
	Max. 95% RH, non-condensing

<b>Safety data</b>	Ambient temperature	-30...50°C [-22...122°F]
	Storage temperature	-40...80°C [-40...176°F]
	Servicing	maintenance-free
<b>Weight</b>	Weight	0.56 kg

## Safety notes



- This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Outdoor application: only possible in case that no (sea) water, snow, ice, insolation or aggressive gases interfere directly with the device and that it is ensured that the ambient conditions remain within the thresholds according to the data sheet at any time.
- Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.
- The device may only be opened at the manufacturer's site. It does not contain any parts that can be replaced or repaired by the user.
- The rotary supports and coupling pieces available as accessories must always be used if transverse forces are likely. In addition, the actuator must not be tightly bolted to the application. It must remain movable via the rotary support (refer to «Installation notes»).
- If the actuator is exposed to severely contaminated ambient air, appropriate precautions must be taken on the system side. Excessive deposits of dust, soot etc. can prevent the gear rod from being extended and retracted correctly.
- If not installed horizontally, the manual override button may only be actuated when there is no pressure on the gear rod.
- To calculate the actuating force required for air dampers and slide valves, the specifications supplied by the damper manufacturers concerning the cross- section and the design, as well as the installation situation and the ventilation conditions must be observed.
- If a rotary support and/or coupling piece is used, actuation force losses are to be expected.
- The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

## Product features

<b>Simple direct mounting</b>	The actuator can be directly connected with the application using the enclosed screws. The head of the gear rod is connected to the moving part of the ventilating application individually on the mounting side or with the Z-KS2 coupling piece provided.
<b>Manual override</b>	Manual override with push-button possible (the gear train is disengaged for as long as the button is pressed or remains locked).
<b>Adjustable stroke</b>	If a stroke limitation will be adjusted, the mechanical operating range on this side of the gear rod can be used starting with an extension length of 20 mm and then can be limited respectively in increments of 20 mm by means of mechanical end stops Z-AS2.
<b>High functional reliability</b>	The actuator is overload protected, requires no limit switches and automatically stops when the end stop is reached.

## Accessories

Mechanical accessories	Description	Type
	End stop kit, Multipack 20 pcs.	Z-AS2
	Rotary support, for linear actuator, for compensation of transverse forces	Z-DS1
	Coupling piece M6	Z-KS2

## Electrical installation



**Supply from isolating transformer.**

**Parallel connection of other actuators possible. Observe the performance data.**


**Wire colours:**

1 = black



2 = red

3 = white

AC/DC 24 V, open/close



AC/DC 24 V, 3-point



## Installation notes



**If a rotary support and/or coupling piece is used, losses in the actuation force losses are to be expected.**

**Applications without transverse forces**

The linear actuator is screwed directly to the housing at three points. Afterwards, the head of the gear rod is fastened to the moving part of the ventilation application (e.g. damper or slide valve).

**Applications with transverse forces**

Connect the coupling piece with the internal thread (Z-KS2) to the head of the gear rod. Screw the rotary support (Z-DS1) to the ventilation application. Afterwards, the linear actuator is screwed to the previously mounted rotary support with the enclosed screw. Then, the coupling piece, which is mounted to the head of the gear rod, is attached to the moving part of the ventilating application (e.g. damper or slide valve). The transverse forces can be compensated for to a certain limit with the rotary support and/or coupling piece. The maximum permissible swivel angle of the rotary support and coupling piece is 10°, laterally and upwards.

## Dimensions

