

3-way butterfly valve (2x butterfly valve with 2x actuator without T-piece), 3-way, Flange, PN 16

- Torque motor 90 Nm
- Nominal voltage AC 24...240 V / DC 24...125 V
- Control Open/close, modulating, communicative, hybrid
- for mixing and diverting applications
- For water-side changeover and control applications
- Communication via BACnet MS/TP, Modbus RTU, Belimo-MP-Bus or conventional control



Picture may differ from product

Type Overview

Type	DN	Kvmax [m³/h]	Kvs [m³/h]	PN
D7100WL/BAC	100	530	160	16
D7125WL/BAC	125	950	280	16
D7150WL/BAC	150	1380	380	16

General technical data can be found on the data sheets for the products D6..WL and JRCA-BAC-S2-T.

Kvmax: for change-over applications

Kvs: for control applications with linear or equal-percentage characteristic curve with opening angle 60% (configured with Belimo Assistant 2).

The maximum flow speed of 4 m/s may not be exceeded in the butterfly valve.

Technical data

Electrical data	Nominal voltage	AC 24...240 V / DC 24...125 V
	Nominal voltage frequency	50/60 Hz
	Nominal voltage range	AC 19.2...264 V / DC 19.2...137.5 V
	Power consumption in operation	40 W
	Power consumption in rest position	14 W
	Power consumption for wire sizing	with 24 V 40 VA / with 240 V 110 VA
Data bus communication	Communicative control	BACnet MS/TP Modbus RTU MP-Bus
	Number of nodes	BACnet / Modbus see interface description MP-Bus max. 16
Functional data	Operating range Y	2...10 V
	Operating range Y variable	0.5...10 V 4...20 mA
	Position feedback U	2...10 V
	Position feedback U variable	0.5...10 V 4...20 mA
	Running time motor	35 s / 90°
	Running time motor variable	20...120 s
	Sound power level motor	60 dB(A)
	Fluid	Water, water with glycol up to max. 50% vol.
	Fluid temperature	-20...120°C [-4...248°F]
	Fluid temperature note	with T-piece ZD7.. -10...120°C [14...248°F]

Technical data

Functional data	Close-off pressure Δp_s	1200 kPa
	Differential pressure Δp_{max}	300 kPa
	Flow	100% opening angle: bypass B – AB: 70% of K_{vmax} value; 60% opening angle: bypass B – AB: 100% of K_{vs} value
	Flow characteristic	0...60% opening angle: equal percentage (VDI/VDE 2173) 0...100% opening angle: S-form
	Flow characteristic note	0...100% opening angle: linear The flow characteristic can be configured to equal percentage or linear using Belimo Assistant 2. The control signal must be inverted for one of the two control paths.
	Leakage rate	tight, leakage rate A (EN 12266-1)
	Pipe connection	Flange according to ISO 7005-1 according to EN 1092-1 according to ISO 7005-2 according to EN 1092-2
	Installation orientation	upright to horizontal (in relation to the spindle)
	Servicing	maintenance-free
	Manual override	hand crank
Safety data	Degree of protection IEC/EN	IP66/67
	Degree of protection NEMA/UL	NEMA 4X
	Housing	UL Enclosure Type 4X
	Pollution degree	3
	Ambient humidity	Max. 100% RH
	Ambient temperature	-30...50°C [-22...122°F]
Materials	Storage temperature	-40...80°C [-40...176°F]
	Valve body	EN-GJS-400-18-LT (GGG 40.3)

Safety notes



- The valve has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Caution: Mains voltage!
- Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.
- Apart from the wiring compartment, the device may only be opened at the manufacturer's site. It does not contain any parts that can be replaced or repaired by the user.
- The device is not designed for applications where chemical influences (gases, fluids) are present or for utilisation in corrosive environments in general.
- The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.
- In case of maintenance work on the hydronic system, the correct valve position must be set via the control signal. Additionally, the actuator has to be disconnected from the power supply. The hand crank and manual override must not be used as a safety measure to maintain the set valve position.

Product features

Operating mode	The 3-way butterfly valve is operated by two multifunctional actuators (for isolation and control applications). Both actuators can be controlled with the same control signal, however, one of the actuators needs to be set up for the use of an inverted control signal. This settings can be made using the Belimo Assistant App. It is recommended to monitor the feedback signal U5 of the actuators to ensure that the 3-way function in the control and bypass path is guaranteed.
Configurable device	For changeover applications, both actuators are configured with either open/close or communicative control. In addition, the control signal of one of the two actuators is set to "inverted". This allows both actuators to be controlled with the same control signal. For control functions, the control can be selected between 2...10 V, 0.5...10 V, 4...20 mA or communicative. The control signal of one of the two actuators is configured to be "inverted", and additionally a Kv setting is made via the limitation of the opening angle.
Manual override	The valve can be manually operated using a hand crank. Unlocking is carried out manually by removing the hand crank.
Combination valve/actuator	Two butterfly valves and two actuators are supplied separately, so that any installation on one T-piece is possible. The T-piece must be ordered separately.

Accessories

Tools	Description	Type
	Service tool for wired and wireless setup, on-site operation and troubleshooting.	Belimo Assistant 2
	Belimo Assistant Link Bluetooth and USB to NFC and MP-Bus converter for configurable and communicative devices	LINK.10
Mechanical accessories	Description	Type
	T-piece for 3-way butterfly valve DN 100	ZD7100
	T-piece for 3-way butterfly valve DN 125	ZD7125
	T-piece for 3-way butterfly valve DN 150	ZD7150


Electrical installation





Caution: Mains voltage!


The wiring of the line for BACnet (MS/TP) has to be carried out in accordance with applicable RS-485 regulations.

Parallel circuit 2...10 V




Electrical installation
Parallel circuit 4...20 mA

Connection BACnet MS/TP / Modbus RTU with analogue primary/secondary operation

Installation notes
Permissible installation orientation

The butterfly valves may be mounted upright to horizontal. The butterfly valves may not be installed in a hanging position i.e. with the spindle pointing downwards.


Installation situation

The two butterfly valves can be mounted in any combination on one T-piece.



Installation notes

Water quality requirements

The water quality requirements specified in VDI 2035 must be adhered to.

Belimo valves are regulating devices. For the valves to function correctly in the long term, they must be kept free from particle debris (e.g. welding beads during installation work). The installation of a suitable strainer is recommended.

Servicing

Butterfly valves and rotary actuators are maintenance-free.


Before any service work on the control element is carried out, it is essential to isolate the rotary actuator from the power supply (by unplugging the electrical cable if necessary). Any pumps in the part of the piping system concerned must also be switched off and the appropriate slide valves closed (allow all components to cool down first if necessary and always reduce the system pressure to ambient pressure level).

The system must not be returned to service until the butterfly valve and the rotary actuator have been reassembled correctly in accordance with the instructions and the pipeline has been refilled by professionally trained personnel.

To avoid a torque increase during off season shut down, exercise the butterfly valve (full open and close) at least once a month.

Flow direction

Direction of flow in both directions possible.



Flow setting

The Belimo butterfly valves have an approximate equal percentage characteristic curve of a 0...60% opening angle. Depending on the desired Kv value, the opening angle can be set with the Belimo Assistant App with a smartphone via Near Field Communication (NFC). Belimo butterfly valves can be ideally used as a control armature.

		10%	20%	30%	40%	50%	60%	70%	80%	90%	100%
DN 100	Kv (m3/h)	1	10	30	55	100	160	245	370	510	530
DN 125	Kv (m3/h)	2	20	50	180	180	280	430	670	940	950
DN 150	Kv (m3/h)	5	45	90	170	255	380	560	760	1250	1380

The Kv values for 3-way valves are calculated values based on Kv values for 2-way valves, considering the pipe friction losses caused by a T-piece.



Configuration linear characteristic curve

The flow characteristic can be set to linear using Belimo Assistant 2.

The following table shows the respective Kv values in relation to the control signal (%).

		10%	20%	30%	40%	50%	60%	70%	80%	90%	100%
DN 100	Kv (m3/h)	53	106	159	212	265	318	371	424	477	530
DN 125	Kv (m3/h)	95	190	285	380	475	570	665	760	855	950
DN 150	Kv (m3/h)	138	276	414	552	690	828	966	1104	1242	1380

The Kv values for 3-way valves are calculated values based on Kv values for 2-way valves, considering the pipe friction losses caused by a T-piece.

Configuration for various applications

The Belimo 3-way butterfly valve can flexibly be used for change-over and control applications. A specific configuration is necessary for each application.

Service



Wireless connection Belimo devices marked with the NFC logo can be operated with Belimo Assistant 2.

Requirement:

- NFC- or Bluetooth-capable smartphone
- Belimo Assistant 2 (Google Play and Apple AppStore)

Align NFC-capable smartphone on the device so that both NFC antennas are superposed.

Connect Bluetooth-enabled smartphone via the Bluetooth-to-NFC converter ZIP-BT-NFC to the device. Technical data and operating instructions are shown in the ZIP-BT-NFC data sheet.


Dimensions


Type	DN	L [mm]	B [mm]	H [mm]	d (PN16) [mm]	K (PN16) [mm]	kg
D7100WL/BAC	100	180	180	335	8 x M16	180	22
D7125WL/BAC	125	200	200	353	8 x M16	210	28
D7150WL/BAC	150	220	220	369	8 x M20	240	32

Further documentation

- Data sheets for butterfly valves
- Data sheets for actuators
- Installation instructions for actuators and/or butterfly valves
- Notes for project planning for butterfly valves
- General notes for project planning
- Data sheet for T-piece
- Tool connections
- BACnet Interface description
- Modbus Interface description
- Quick Guide – Belimo Assistant 2