

Modulating rotary actuator with fail-safe for ball valves and butterfly valves

- Torque motor 20 Nm
- Nominal voltage AC/DC 24 V
- Control modulating 0.5...10 V
- Position feedback 0.5...10 V
- Deenergised closed (NC)
- With 2 integrated auxiliary switches



Picture may differ from product

## Technical data

Electrical data	
	Nominal voltage
	AC/DC 24 V
	Nominal voltage frequency
	50/60 Hz
	Nominal voltage range
	AC 19.2...28.8 V / DC 21.6...28.8 V
	Power consumption in operation
	5.5 W
	Power consumption in rest position
	3 W
	Power consumption for wire sizing
	8.5 VA
	Auxiliary switch
	2x SPDT, 1x 10% / 1x 11...100%
	Switching capacity auxiliary switch
	1 mA...3 A (0.5 A inductive), DC 5 V...AC 250 V
	Connection supply / control
	Cable 1 m, 4x 0.75 mm <sup>2</sup>
	Connection auxiliary switch
	Cable 1 m, 6x 0.75 mm <sup>2</sup>
	Parallel operation
	Yes (note the performance data)
Functional data	
	Torque motor
	20 Nm
	Torque fail-safe
	20 Nm
	Operating range Y
	0.5...10 V
	Input impedance
	100 kΩ
	Position feedback U
	0.5...10 V
	Position feedback U note
	Max. 0.5 mA
	Position accuracy
	±5%
	Direction of motion motor
	Y = 0 (0 V = A – AB = 0%)
	Direction of motion fail-safe
	Deenergised NC, valve closed (A – AB = 0%)
	Direction of motion note
	for valves with L-bore (A – AB = 100%)
	Manual override
	by means of hand crank and locking switch
	Running time motor
	90 s / 90°
	Running time fail-safe
	<20 s @ -20...50°C, <60 s @ -30°C
	Sound power level, motor
	45 dB(A)
	Position indication
	Mechanical
	Service life
	Min. 60'000 fail-safe positions
Safety data	
	Protection class IEC/EN
	III, Safety Extra-Low Voltage (SELV)
	Power source UL
	Class 2 Supply
	Protection class auxiliary switch IEC/EN
	II, reinforced insulation
	Degree of protection IEC/EN
	IP54
	Degree of protection NEMA/UL
	NEMA 2
	Housing
	UL Enclosure Type 2
	EMC
	CE according to 2014/30/EU

<b>Safety data</b>	Low voltage directive	CE according to 2014/35/EU
	Certification IEC/EN	IEC/EN 60730-1 and IEC/EN 60730-2-14
	UL Approval	cULus according to UL60730-1A, UL60730-2-14 and CAN/CSA E60730-1
		The UL marking on the actuator depends on the production site, the device is UL-compliant in any case
	Type of action	Type 1.AA.B
	Rated impulse voltage supply / control	0.8 kV
	Rated impulse voltage auxiliary switch	2.5 kV
	Pollution degree	3
	Ambient humidity	Max. 95% RH, non-condensing
	Ambient temperature	-30...50°C [-22...122°F]
	Storage temperature	-40...80°C [-40...176°F]
	Servicing	maintenance-free
<b>Mechanical data</b>	Connection flange	F05
<b>Weight</b>	Weight	2.5 kg

## Safety notes



- This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Outdoor application: only possible in case that no (sea) water, snow, ice, insulation or aggressive gases interfere directly with the device and that it is ensured that the ambient conditions remain within the thresholds according to the data sheet at any time.
- Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.
- The device may only be opened at the manufacturer's site. It does not contain any parts that can be replaced or repaired by the user.
- Cables must not be removed from the device.
- The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.
- The two switches integrated in the actuator are to be operated either on mains voltage or on safety extra-low voltage. The combination mains voltage/safety extra-low voltage is not permitted.

## Product features

<b>Operating mode</b>	The actuator is controlled with a control signal Y (note the operating range). The actuator moves the valve to the operating position at the same time as tensioning the return spring. The valve is turned back to the fail-safe position by spring force when the supply voltage is interrupted.
<b>Simple direct mounting</b>	Simple direct mounting on the rotary valve or butterfly valve with mounting flange. The mounting orientation in relation to the fitting can be selected in 90° steps.
<b>Manual override</b>	By using the hand crank the valve can be operated manually and engaged with the locking switch at any position. Unlocking is carried out manually or automatically by applying the operating voltage.
<b>Adjustable angle of rotation</b>	Adjustable angle of rotation with mechanical end stops.

## Product features

**High functional reliability** The actuator is overload protected, requires no limit switches and automatically stops when the end stop is reached.

**Flexible signalling** The actuator has one auxiliary switch with a fixed setting and one adjustable auxiliary switch. They permit a 10% or 11...100% angle of rotation to be signaled.

## Electrical installation



Supply from isolating transformer.

Parallel connection of other actuators possible. Observe the performance data.

## Wire colours:

1 = black

2 = red

3 = white

5 = orange

S1 = violet

S2 = red



S3 = white

S4 = orange


S5 = pink

S6 = grey


## AC/DC 24 V, modulating



## Auxiliary switch



## Operating controls and indicators



## Auxiliary switch settings

**Note:** Perform settings on the actuator only in deenergised state.

For the auxiliary switch position settings, carry out points 1 to 7 successively.

**1 Manual override**

Turn the hand crank until the desired switching position is set.

**2 Shaft clamp**

Edge line A displays the desired switching position of the actuator on the scale.

**3 Fasten the locking device**

Turn the locking switch to the „Locked padlock“ symbol.

**4 Auxiliary switch**

Turn rotary knob until the notch points to the arrow symbol.

**5 Unlock the locking device**

Turn the locking switch to the „Unlocked padlock“ symbol or unlock with the hand crank.


**6 Cable**

Connect continuity tester to S4 + S5 or to S4 + S6.

**7 Manual override**

Turn the hand crank until the desired switching position is set and check whether the continuity tester shows the switching point.

## Dimensions



## Further documentation

- The complete product range for water applications
- Data sheets for rotary valves and butterfly valves
- Installation instructions for actuators and/or rotary valves and butterfly valves
- General notes for project planning