

Stem heater for ball valve DN 15...50

- for temperatures down to -10° C



Picture may differ from product

## Technical data

<b>Electrical data</b>	Nominal voltage	AC/DC 24 V
	Nominal voltage frequency	50/60 Hz
	Power consumption heating	20 W
	Connection supply	Cable 1 m
	Electrical connection	Cable
<b>Functional data</b>	Fluid temperature	-10...20°C [14...68°F]
<b>Safety data</b>	Degree of protection IEC/EN	IP20
	Ambient temperature	-10...50°C [14...122°F]
	Servicing	maintenance-free
<b>Weight</b>	Weight	0.04 kg
<b>Materials</b>	Used materials	Silicone

## Safety notes



- This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.
- The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

## Dimensions

Type	Weight
ZR24-2	0.04 kg