


Customizable Fail-Safe actuator for controlling dampers in typical commercial HVAC applications.

- Torque motor 180 in-lb [20 Nm]
- Nominal voltage AC 24...240 V / DC 24...125 V
- Control On/Off
- NEMA 4X



5-year warranty



## Technical data

Electrical data	Nominal voltage	AC 24...240 V / DC 24...125 V
	Nominal voltage frequency	50/60 Hz
	Nominal voltage range	AC 19.2...264 V / DC 21.6...137.5 V
	Power consumption in operation	7 W
	Power consumption in rest position	3.5 W
	Electrical Connection	18 AWG appliance cables, 1 m, 3 m or 5 m, with 1/2" NPT conduit connector
	Overload Protection	electronic throughout 0...95° rotation
	Electrical Protection	actuators are double insulated
Functional data	Torque motor	180 in-lb [20 Nm]
	Direction of motion motor	selectable by ccw/cw mounting
	Direction of motion fail-safe	reversible with cw/ccw mounting
	Manual override	5 mm hex crank (3/16" Allen), supplied
	Angle of rotation	95°
	Angle of rotation note	adjustable with mechanical end stop, 35...95°
	Running Time (Motor)	75 s / 90°
	Running time fail-safe	<20 s @ -20...50°C, <60 s @ -30°C
	Noise level, motor	50 dB(A)
	Noise level, fail-safe	62 dB(A)
Safety data	Position indication	Mechanical, 5...20 mm stroke
	Power source UL	Class 2 Supply
	Degree of protection NEMA/UL	NEMA 4X
	Housing	UL Enclosure Type 4X
	Agency Listing	cULus acc. to UL60730-1A/-2-14, CAN/CSA E60730-1:02, CE acc. to 2014/30/EU and 2014/35/EU
	Quality Standard	ISO 9001
	Ambient humidity	Max. 100% RH
	Ambient temperature	-22...122°F [-30...50°C]
	Ambient temperature note	-40...50°C [104...122°F] for actuator with integrated heating
	Storage temperature	-40...176°F [-40...80°C]

<b>Safety data</b>	Servicing	maintenance-free
<b>Weight</b>	Weight	9.6 lb [4.4 kg]
<b>Materials</b>	Housing material	Polycarbonate
<b>Footnotes</b>	†Rated Impulse Voltage 4kV, Type of action 1.AA, Control Pollution Degree 4.	

## Product features

<b>Application</b>	For On/Off, fail-safe control of dampers in HVAC systems. Actuator sizing should be done in accordance with the damper manufacturer's specifications. Control is On/Off from an auxiliary contact or a manual switch. The actuator is mounted directly to a damper shaft up to 1.05" in diameter by means of its universal clamp. Maximum of two AF's can be piggybacked for torque loads of up to 266 in-lbs. Minimum 3/4" diameter shaft and parallel wiring.
<b>Operation</b>	<p>The AF..UP N4 series actuators provide true spring return operation for reliable fail-safe application and positive close off on air tight dampers. The spring return system provides constant torque to the damper with, and without, power applied to the actuator. The AF..UP N4 series provides 95° of rotation and is provided with a graduated position indicator showing 0° to 95°. The actuator may be stalled anywhere in its normal rotation without the need of mechanical end switches. The AF..UP N4 actuator is shipped at 5° (5° from full fail-safe) to provide automatic compression against damper gaskets for tight shut-off.</p> <p>Installation Note: Use suitable flexible metallic conduit or its equivalent with the conduit fitting. Not suitable for plenum applications.</p> <p>For low ambient temperatures, the optional supplemental (-Y) Heater add-on is available.</p>
<b>Typical specification</b>	On/Off spring return damper actuators shall be direct coupled type which require no crank arm and linkage and be capable of direct mounting to a jackshaft up to a 1.05" diameter. The actuators must be designed so that they may be used for either clockwise or counter clockwise fail-safe operation. Actuators shall be protected from overload at all angles of rotation. If required, two SPDT auxiliary switch shall be provided having the capability of one being adjustable. Actuators with auxiliary switches must be constructed to meet the requirements for Double Insulation so an electrical ground is not required to meet agency listings. Actuators shall be cULus listed and have a 5 year warranty, and be manufactured under ISO 9001 International Quality Control Standards. Actuators shall be as manufactured by Belimo.

## Peripheral devices

Description	Type
Cable conduit connector 1/2"	TF-CC US
Wrench 0.32 in and 0.39 in [8 mm and 10 mm]	TOOL-06
Mounting bracket for AF..	ZG-100
Mounting bracket for AF / NF	ZG-101
Mounting bracket for AF / NF	ZG-118
Mounting kit for foot mount installation	ZG-AFB118
Weather shield 13x8x6" [330x203x152 mm] (LxWxH)	ZS-100
Weather shield 406x213x102 mm [16x8-3/8x4"] (LxWxH)	ZS-150
Explosion proof housing 16x10x6.435" [406x254x164 mm] (LxWxH), UL and CSA, Class I, Zone 1&2, Groups B, C, D, (NEMA 7), Class III, Hazardous (classified) Locations	ZS-260
Weather shield 17-1/4x8-3/4x5-1/2" [438x222x140 mm] (LxWxH), NEMA 4X, with mounting brackets	ZS-300

## Accessories


	Tools	Description	Type
Electrical accessories		Signal simulator, Power supply AC 120 V	PS-100
		<b>Description</b>	<b>Type</b>
		Gasket for cable gland (NEMA 4 models)	11097-00001
		Cable Gland (NEMA 4 models)	43442-00001
Mechanical accessories		Auxiliary switch, mercury-free	P475
		Auxiliary switch, mercury-free	P475-1
		<b>Description</b>	<b>Type</b>
		Anti-rotation bracket, for AF / NF	AF-P
Factory add-on option only		Ball joint suitable for damper crank arm KH8 / KH10	KG10A
		Damper crank arm Slot width 8.2 mm, clamping range $\varnothing 14...25$ mm	KH10
		Push rod for KG10A ball joint L 36", 3/8" diameter	SH10
		Wrench 0.32 in and 0.39 in [8 mm and 10 mm]	TOOL-06
		Wrench 0.512 in. [13 mm]	TOOL-07
			ZG-DC1
			ZG-DC2
		1" diameter jackshaft adaptor (11" L).	ZG-JSA-1
		1-5/16" diameter jackshaft adaptor (12" L).	ZG-JSA-2
		1.05" diameter jackshaft adaptor (12" L).	ZG-JSA-3
		<b>Description</b>	<b>Type</b>
		Heater, with adjustable thermostat	ACT_PACK_H
		Heater, with adjustable thermostat	ACT_PACK_Y

## Electrical installation

## Wire colors:

1 = blue

2 = brown

AC 24...240 V / DC 24...125 V, on/  
off


## Dimensions

PC

