

Modulating damper actuator for adjusting dampers in technical building installations

- Air damper size up to approx. 4 m²
- Torque motor 20 Nm
- Nominal voltage AC/DC 24 V
- Control modulating 2...10 V
- Position feedback 2...10 V



Picture may differ from product

Technical data

Electrical data	
Nominal voltage	AC/DC 24 V
Nominal voltage frequency	50/60 Hz
Nominal voltage range	AC 19.2...28.8 V / DC 19.2...28.8 V
Power consumption in operation	2 W
Power consumption in rest position	0.4 W
Power consumption for wire sizing	4 VA
Connection supply / control	Cable 1 m, 4x 0.75 mm ²
Parallel operation	Yes (note the performance data)
Functional data	
Torque motor	20 Nm
Operating range Y	2...10 V
Input impedance	100 kΩ
Position feedback U	2...10 V
Position feedback U note	Max. 1 mA
Position accuracy	±5%
Direction of motion motor	selectable with switch 0/1
Direction of motion note	Y = 0 V: At switch position 0 (ccw rotation) / 1 (cw rotation)
Manual override	with push-button, can be locked
Angle of rotation	Max. 95°
Angle of rotation note	can be limited on both sides with adjustable mechanical end stops
Running time motor	150 s / 90°
Sound power level, motor	45 dB(A)
Mechanical interface	Universal shaft clamp reversible 10...20 mm
Position indication	Mechanical, pluggable
Safety data	
Protection class IEC/EN	III, Safety Extra-Low Voltage (SELV)
Power source UL	Class 2 Supply
Degree of protection IEC/EN	IP54
Degree of protection NEMA/UL	NEMA 2
Housing	UL Enclosure Type 2
EMC	CE according to 2014/30/EU
Low voltage directive	CE according to 2006/95/EC
Certification IEC/EN	IEC/EN 60730-1 and IEC/EN 60730-2-14

Safety data	UL Approval	cULus according to UL60730-1A, UL60730-2-14 and CAN/CSA E60730-1 The UL marking on the actuator depends on the production site, the device is UL-compliant in any case
Hygiene test		According to VDI 6022 Part 1 / SWKI VA 104-01, cleanable and disinfectable, low emission
Type of action	Type 1	
Rated impulse voltage supply / control	0.8 kV	
Pollution degree	3	
Ambient humidity	Max. 95% RH, non-condensing	
Ambient temperature	-30...50°C [-22...122°F]	
Storage temperature	-40...80°C [-40...176°F]	
Servicing	maintenance-free	
Weight	Weight	0.95 kg

Safety notes



- This device has been designed for use in stationary heating, ventilation and air-conditioning systems and must not be used outside the specified field of application, especially in aircraft or in any other airborne means of transport.
- Outdoor application: only possible in case that no (sea) water, snow, ice, insolation or aggressive gases interfere directly with the device and that it is ensured that the ambient conditions remain within the thresholds according to the data sheet at any time.
- Only authorised specialists may carry out installation. All applicable legal or institutional installation regulations must be complied with during installation.
- The device may only be opened at the manufacturer's site. It does not contain any parts that can be replaced or repaired by the user.
- Cables must not be removed from the device.
- To calculate the torque required, the specifications supplied by the damper manufacturers concerning the cross-section and the design, as well as the installation situation and the ventilation conditions must be observed.
- The device contains electrical and electronic components and must not be disposed of as household refuse. All locally valid regulations and requirements must be observed.

Product features

Operating mode	The actuator is controlled with a control signal Y (note the operating range) and drives to the position defined by the control signal. Measuring voltage U serves for the electrical display of the damper position 0...100% and as control signal for other actuators.
Simple direct mounting	Simple direct mounting on the damper shaft with a universal shaft clamp, supplied with an anti-rotation mechanism to prevent the actuator from rotating.
Manual override	Manual override with push-button possible (the gear train is disengaged for as long as the button is pressed or remains locked).
Adjustable angle of rotation	Adjustable angle of rotation with mechanical end stops.
High functional reliability	The actuator is overload protected, requires no limit switches and automatically stops when the end stop is reached.

Accessories

Electrical accessories	Description	Type
Auxiliary switch 1x SPDT add-on		S1A
Auxiliary switch 2x SPDT add-on		S2A
Feedback potentiometer 140 Ω add-on		P140A
Feedback potentiometer 1 k Ω add-on		P1000A
Feedback potentiometer 10 k Ω add-on		P10000A
Signal converter voltage/current 100 k Ω 4...20 mA, Supply AC/DC 24 V		Z-UIC
Positioner for wall mounting		SGA24
Positioner for built-in mounting		SGE24
Positioner for front-panel mounting		SGF24
Positioner for wall mounting		CRP24-B1
Mechanical accessories	Description	Type
Actuator arm for standard shaft clamp (reversible)		AH-20
Shaft extension 240 mm \varnothing 20 mm for damper shaft \varnothing 12...21 mm CrNi		AV12-25-I
Shaft extension 240 mm \varnothing 20 mm for damper shaft \varnothing 8...22.7 mm		AV8-25
Ball joint suitable for damper crank arm KH8		KG8
Ball joint suitable for damper crank arm KH8 / KH10		KG10A
Damper crank arm Slot width 8.2 mm, clamping range \varnothing 10...18 mm		KH8
Shaft clamp one-sided, clamping range \varnothing 8...26 mm, Multipack 20 pcs.		K-ENSA
Shaft clamp one-sided, clamping range \varnothing 12...26 mm, for CrNi shaft (INOX), Multipack 20 pcs.		K-ENSA-I
Shaft clamp reversible, clamping range \varnothing 10...20 mm		K-SA
Anti-rotation mechanism 180 mm, Multipack 20 pcs.		Z-ARS180
Anti-rotation mechanism 230 mm, Multipack 20 pcs.		Z-ARS230
Form fit insert 10x10 mm, Multipack 20 pcs.		ZF10-NSA
Form fit insert 12x12 mm, Multipack 20 pcs.		ZF12-NSA
Form fit insert 15x15 mm, Multipack 20 pcs.		ZF15-NSA
Form fit insert 16x16 mm, Multipack 20 pcs.		ZF16-NSA
Mounting kit for linkage operation for flat installation		ZG-SMA
Position indicator, Multipack 20 pcs.		Z-PI
Baseplate extension for SM..A to SM../AM../SMD24R		Z-SMA

Electrical installation



Supply from isolating transformer.

Parallel connection of other actuators possible. Observe the performance data.

Wire colours:

1 = black



2 = red

3 = white

5 = orange

Electrical installation


AC/DC 24 V, modulating



Dimensions

Spindle length

	Min. 48
	Min. 20 mm [0.75"]



Clamping range

	10...20	≥ 10	≤ 20
CrNi (INOX)	12...20	≥ 10	≤ 20

When using a round shaft made of CrNi (INOX): $\varnothing 12...20$ mm

