

- Combination of 94 mm cubic-design multi-tone alarm sounder and LED strobe beacon
- Strobe beacon with good frontal/lateral signalling effect
- High degree of protection IP 66
- 32 tones can be selected, 3 tones can be switched externally
- Max. 108 dB (A) sound pressure, infinitely adjustable
- 4 different strobe patterns, can be switched externally
- For commercial, industrial, and general applications



EXT-AS-HS-CLR



EXT-AS-HS-BLU



EXT-AS-HS-AMB

Technical Data - LED Strobe Beacon

Housing	94 mm (square), Polycarbonate red (RAL 3000)
Lens	Polycarbonate, ribbed inside blue, amber, or clear
Type of mounting	any
Cable entry	Back: Grommet 5...10 mm, optional side cable entry with cable gland (on both sides) (accessory type AKV)
Connection technology	Screw/plug-in terminal 2.5 mm ²
Leakage current	0.003 A (PLC-suitable)
Beacon type	LED multi-strobe beacon
Light source	High Power LEDs
Strobe/flash frequency	Double strobe 1.4 Hz; 6x strobe 1.0 Hz; multi-strobe
Duty cycle	100%
Service life	Light source: >50.000 h
Operating temperature	-30°C / +60°C
Degree of protection	IP66 & UL Type 4/4x/13
Impact resistance	IK09
Weight	1.7 kg

Technical Data - Multi-Tone Alarm Sounder

Housing	Polycarbonate red (RAL 3000)
Type of mounting	Any, sound outlet opening at bottom or horizontal
Cable entry	Back: Grommet 5...10 mm, Side: AKV cable gland M20 x 1.5 7...14 mm can be mounted
Connection technology	Screw/plug-in terminal up to 2.5 mm ²
Leakage current	0.003 A
Tone	32 Tones, 3 Tones can be switched externally, see tone table
Volume	108 dB (can be adjusted with potentiometer)
Tone frequency	150...2.900 Hz
Duty cycle	100%
Operating temperature	-30°C / +60°C
Degree of protection	IP66 & UL Type 4/4x/13
Impact resistance	IK09
Weight	300 g

Dimensions
