



Modbus Interface Description



VAV-Compact Volumetric flow compact control device

Edition 2023-12 / V3.08

Contents

Modbus general notes

General information	
Modbus RTU	
Parametrisation	
Register implementation	4
Supported commands	
Command "Read Discrete Inputs"	
Interpret values in the registers	
32-bit values in two registers	5

Modbus register overview

Operation, Service	6
--------------------	---

Modbus register description

7-9

Modbus general notes

General information

Date	01.12.2023
Product Name	VAV-Compact
Actuator Type	..MV-D3-MOD, ..HV24A-MOD
Protocol	Modbus RTU over RS-485

Modbus RTU

Transmission Formats	1-8-N-2, 1-8-N-1, 1-8-E-1, 1-8-O-1 (Default: 1-8-N-2)
Baud Rates	9'600, 19'200, 38'400, 76'800, 115'200 Bd (Default: 38'400 Bd)
Address	1...247 (Default: 1)
Number of Nodes	Max. 32 (without repeater)
Terminating Resistor	120 Ω

Parametrisation

Tool	ZTH EU
------	--------

Quick addressing

Actuators support quick addressing via the "Address" and "Adaption" buttons. For detailed information, please see product datasheet (chapter Service).

Register implementation

All data is arranged in a table and addressed by 1..n (Register No.) or 0..n-1 (Address). No distinction is made between data types (Discrete Inputs, Coils, Input Registers and Holding Registers). As a consequence, all data can be accessed with the two commands for Holding Register. The commands for Discrete Inputs and Input Registers can be used as an alternative.

Supported commands

Standard commands:	Optional commands:
Read Holding Registers [3]	Read Discrete Inputs [2]
Write Single Register [6]	Read Input Registers [4]
	Write Multiple Registers [16]

Command "Read Discrete Inputs"

The command reads one or more bits and can alternatively be used for Register No. 105 (Malfunction and Service Information).

Example:

The start address to be used is 1664 -> **104** (Register Address) * **16** (Bit) = **1664**

Interpret values in the registers

All values in the register are unsigned integer data types.

Example:

Read (Function 03, 1 Register)
Value Register No. x
= 0001 1010 1100 1000₂
= 6,856₁₀

Actual value
= value * scaling factor * unit
= 6,856 * 0.01 * unit
= **68.56 unit**

32-bit values in two registers

Values that exceed 65,535 are stored in two consecutive Registers and have to be interpreted as "little endian" / LSW (Least Significant Word) first.

Example:

Register No. x (Value LowWord)	Register No. x + 1 (Value HighWord)
= 14,551 ₁₀	= 19 ₁₀
= 0011 1000 1101 0111 ₂	= 0000 0000 0001 0011 ₂

Value LowWord = 14,551 = 0011 1000 1101 0111 ₂	Value HighWord = 19 = 0000 0000 0001 0011 ₂
--	---

32-bit value
 = 0000 0000 0001 0011 0011 1000 1101 0111₂
 = 1,259,735₁₀
 = **1,259.735 unit**

Math formula:

32-bit value = (Value HighWord * 65,536) + Value LowWord
 32-bit value = (19 * 65,536) + 14,551
 = 1,259,735
 = 1,259.735 unit

Deactivated registers

If a register is not supported by a device or by a device setting, this is indicated by 65,535 (1111 1111 1111 1111₂).

Modbus register overview

Operation

No.	Address	Register	Access
1	0	Setpoint [%]	R / W
2	1	Override Control	R / W
3	2	Command	R / W
4	3	Actuator Type	R
5	4	Relative Position [%]	R
6	5	Absolute Position [°] [mm]	R
7	6	Relative Volumetric Flow [%]	R
8	7	Absolute Volumetric Flow [m ³ /h]	R
9	8	Sensor Value 1 [mV] [-]	R
10	9	-	-
11	10	Absolute Flow in unit selected	LowWord
12	11		HighWord
13	12	Analog Setpoint [%]	R

Service

No.	Address	Register	Access
100	99	Bus Termination	R
101	100	Series Number 1 st part	
102	101	Series Number 2 nd part	R
103	102	Series Number 4 th part	
104	103	Firmware Version	R
105	104	Malfunction and Service Information	R
106	105	Min [%]	R
107	106	Max [%]	R / W
108	107	Sensor Type 1	R / W
109	108	Bus Fail Position	R / W
110	109	Communication Watchdog	R / W
111	110	Nominal Volumetric Flow [m ³ /h]	-
112	111	-	-
113	112	Nominal Volumetric Flow in unit selected	LowWord
114	113		HighWord
115	114	-	-
116	115	-	-
117	116	Control Mode	R / W
118	117	Unit Selection Flow	R / W
119	118	Setpoint Source	R / W



All writeable registers >100 are persistent and are **not** supposed to be written on a regular basis.

Modbus register description

No.	Address	Description Comment	Range, enumeration	Unit	Scaling	Access
1	0	Setpoint Setpoint for actuator between 0 and Max (No. 107)	0...10'000 Default: 0	%	0.01	R / W
2	1	Override control Overrides setpoint with defined values. Use of Fast open / Fast close: Fast open and Fast close cycles lead to increased mechanical load. Usage should be limited to certain time-critical events (e.g. frost protection).	0: None 1: Open 2: Close 3: Min 4: Mid 5: Max 6: Fast open 7: Fast close Default: None(0)	–	–	R / W
3	2	Command Initiation of actuator functions for service and test. After command is sent, register returns to None(0). With Reset(4), all alfunction and service information (Register No. 105) can be reset.	0: None 1: Adaption 2: Test 3: Sync 4: Reset Default: None(0)	–	–	R / W
4	3	Actuator type	0: Actuator not connected 1: Air / water 2: VAV / EPIV 3: Fire 4: Energy Valve 5: 6way EPIV	–	–	R
5	4	Relative position	0...10'000	%	0.01	R
6	5	Absolute position The unit depends on the device: [°] for actuators with rotary movement [mm] for actuators with linear movement	0...max angle / stroke	° mm	1 1	R
7	6	Relative volumetric flow Relative volumetric flow of $V_{n'om}$	0...10'000	%	0.01	R
8	7	Absolute volumetric flow	0... V'_{nom}	m ³ /h Pa	1	R
9	8	Sensor 1 value Current value of sensor 1, depending on the setting of the Sensor 1 type (Register No. 108) [mV] if Sensor 1 type (Register No. 108) is Active(1) [0 / 1] if Sensor 1 type (Register No. 108) is Switch(4)	0...65'535	mV –	0 / 1	R
10	9	–	–	–	–	–
11	10	Absolute volumetric flow Absolute flow in unit selected (Register No. 118) LowWord Lower 16 bit of 32-bit value	–	UnitSel	0.001	R
12	11	Absolute volumetric flow Absolute flow in unit selected (Register No. 118) HighWord Upper 16 bit of 32-bit value	–	UnitSel	0.001	R
13	12	Analog setpoint Shows the setpoint in % if actuator is controlled by analog signal.	0...10'000	%	0.01	R

No.	Address	Description Comment	Range, enumeration	Unit	Scaling	Access
100	99	Bus termination Indicates if bus termination (120 Ω) is enabled. Bus termination can be set with the configuration tools.	0: Inactive 1: Active Default: Inactive(0)	-	-	R
101	100	Series number 1st part Each device has an unambiguous series number, which is either impressed on or glued to the housing. The series number consists of 4 segments, although only parts 1, 2 and 4 are displayed on Modbus. Example: 00839-31324-064-008 1 st part: 00839 2 nd part: 31324 4 th part: 008	-	-	-	R
102	101	Series number 2nd part	-	-	-	R
103	102	Series number 4th part	-	-	-	R
104	103	Firmware version Firmware version of communication module Example: 302, Version 3.02	-	-	-	R
105	104	Malfunction and service information Value is bit-coded. More than one bit can be set to 1. Not all bits mentioned in the enumeration are used for this actuator range. 1: Mechanical travel increased: The actuator has been moved outside the adapted working range. 2: Actuator cannot move: Mechanical overload, e.g. blocked actuator, etc. 8: Internal activity: Actuator performs a test run, adaptation, etc. 9: Gear train disengaged: The manual override button is pressed. 10: Bus Watchdog triggered: Timeout for the Bus Watchdog expired.	Bitmask = Bit0: - Bit1: Mechanical travel increased Bit2: Actuator cannot move Bit3: - Bit4: - Bit5: - Bit6: - Bit7: - Bit8: Internal activity Bit9: Gear train disengaged Bit10: Bus Watchdog triggered Bit11: - Bit12: - Bit13: - Bit14: - Bit15: -	-	-	R
106	105	V_{min} Min has to be ≤ Max	0...V _{max} Default: 0	%	0.01	R / W
107	106	V_{max} Max has to be ≥ Min and >20%	V _{min} ...10'000 Default: 10'000	%	0.01	R / W
108	107	Sensor 1 type If Setpoint Source (Register No. 119) is Analog (hybrid mode), the sensor type 1 can be set to Active(1) in order to see the Analog Setpoint in mV. Note: After changing the sensor type, it might be necessary to restart the actuator in order for correct sensor values to be read out. For setting "4: Switch" it is mandatory that the control signal is parametrised to 2...10 V.	0: None 1: Active / hybrid 2: - 3: - 4: Switch Default: None(0)	-	-	R / W

No.	Address	Description Comment	Range, enumeration	Unit	Scaling	Access
109	108	Bus fail position Modbus communication is not monitored by default. In the event of a breakdown in communication, the actuator retains the current setpoint. The bus implementation tracks the Modbus communication. If neither the Setpoint (Register No. 1) nor the Override Control (Register No. 2) is renewed before the timeout for Bus Watchdog (Register No. 110) expires, the actuator moves to the Bus Fail Position. Triggered bus watchdog is indicated in the Malfunction and Service Information (Register No. 105). In hybrid mode (SpSource (Register No. 119) = Analog), bus monitoring is not activated.	0: None / last setpoint 1: Fast close 2: Fast open 3: Mid position (parametrised) Default: None(0)	–	–	R / W
110	109	Timeout for bus watchdog in s Time until Bus Fail will be detected. If Bus Watchdog = 0 then deactivated If Bus Fail Position (Register No. 109) different from 0, the Bus Fail Position becomes active after the Timeout for Bus Watchdog has expired.	0...3'600 Default: 0 If Bus Fail Position (Register No. 109) not None(0), then Default: 120	s	1	R / W
111	110	Nominal volumetric flow	–	m ³ /h	1	R
112	111	–	–	–	–	–
113	112	Nominal volumetric flow V _{nom} in unit selected (Register No. 118) LowWord Lower 16 bit of 32-bit value	–	UnitSel	0.001	R
114	113	Nominal volumetric flow V _{nom} in unit selected (Register No. 118) HighWord Upper 16 bit of 32-bit value	–	–	–	–
115	114	–	–	–	–	–
116	115	–	–	–	–	–
117	116	Control mode	0: Position control 1: Flow control	–	–	R / W
118	117	Unit selection flow	0: m ³ /s 1: m ³ /h 2: l/s 3: l/min 4: l/h 5: gpm 6: cfm Default: m ³ /h(1)	–	–	R / W
119	118	Setpoint source Analog: Setpoint from analog signal 0...10 V on wire 3. Bus: Setpoint from Modbus (Register No. 1).	0: Analog 1: Bus Default: Bus(1)	–	–	R / W

Description Access: R = Read, W = Write

All inclusive.

Belimo as a global market leader develops innovative solutions for the controlling of heating, ventilation and air-conditioning systems. Damper actuators, control valves, sensors and meters represent our core business.

Always focusing on customer value, we deliver more than only products. We offer you the complete product range for the regulation and control of HVAC systems from a single source. At the same time, we rely on tested Swiss quality with a five-year warranty. Our worldwide representatives in over 80 countries guarantee short delivery times and comprehensive support through the entire product life. Belimo does indeed include everything.

The "small" Belimo devices have a big impact on comfort, energy efficiency, safety, installation and maintenance.

In short: Small devices, big impact.



5-year warranty



On site around the globe



Complete product range



Tested quality



Short delivery times



Comprehensive support



BELIMO Automation AG

Brunnenbachstrasse 1, 8340 Hinwil, Switzerland
+41 43 843 61 11, info@belimo.ch, www.belimo.com

BELIMO[®]