

Current transducer, split core,
multi-range, DC 0...10 V terminal output



Technical data

| | |
|-----------------------|---|
| Operating Temperature | -30...140°F |
| Humidity Range | 5...95% (non-condensing) |
| Max Sense Voltage | AC 600 V |
| Mounting/Installation | Removable mounting tab provided. The wire clamp locks against the wire being monitored, securing the unit in place. |
| Sensor Type | split core with voltage output |
| Origin | Made of US and non-US parts |
| Accuracy | 98.8% full scale |
| Loading | 0...20 amps: 5% error @ 60.4 kΩ 0...50 amps: 5% error @ 25.24 kΩ 0...100 amps: 5% error @ 13.65 kΩ |
| Sensing Range | 0...20 amps, 50 amps, 100 amps |
| Terminal Output | DC 0...10 V |
| Approvals | UL Listed, UL916, UL864, C-UL, CE, RoHS, California State Fire Marshall |

DIP Switches

| 1 | 2 | Sensing Range |
|-----|-----|---------------|
| OFF | OFF | 0...20 amps |
| OFF | ON | 0...50 amps |
| ON | OFF | 0...100 amps |

Dimensions

