

Belimo's gas monitoring devices offer an intelligent peer-to-peer communication protocol that gives users unparalleled flexibility to configure and install a complete ventilation control system with only one monitor or dozens operating in multiple ventilation zones. With field-replaceable sensing elements, on-demand ventilation, stand-alone installation, integrated and lockable LCDs, Belimo's gas monitoring devices are an ideal choice for any application involving vehicle exhaust.



2-year warranty



Vue d'ensemble

Type	Valeurs mesurées	Nombre de relais	Signal de sortie actif du gaz	Communication
EXT-OP-6002-A	CO	1	2x 2...10 V, 2x 4...20 mA	CAN bus, BACnet MS/TP
EXT-OP-6002-B	CO	2	-	CAN bus, BACnet MS/TP
EXT-OP-6002-C	CO	0	-	CAN bus

Données techniques

Caractéristiques électriques

Tension nominale	AC/DC 24 V
Fréquence de tension nominale	50/60 Hz
Plage de tension nominale	AC 17...28 V/DC 17...28 V
Consommation d'énergie CA	5 VA
Consommation d'énergie CC	5 W
Spécifications des câbles	1 paire torsadée blindée 24..18 AWG
Fusible de sûreté	Thermistance à coefficient de température positif, remise à zéro automatique


Caractéristiques fonctionnelles

Solution	air
Communication	CAN bus BACnet MS/TP
Remarque sur le signal de sortie actif	2...10 V or 4...20 mA output, selectable with jumper
Remarque relative au signal de sortie du relais	1 x SPDT, max. 1.5 A (0.4 A inductif), AC 250 V
Montage	1,3 m [4 pi] au-dessus du plancher
Altitude max.	2 000 m [6 562 pi] au dessus du niveau de la mer
Zone de couverture	Rayon : 15 m [50 pi] Superficie : 700 m ² [7500 pi ²] Il ne peut y avoir d'obstacles tels que des murs, des escaliers, des ascenseurs, des étagères pleines, des coffres à outils, etc.


Caractéristiques fonctionnelles	Affichage	ACL, avec rétro-éclairage, Teneur en gaz, état du système
	Alarme	Alarme sonore, 85 db à 1 m [3.3 ft]
Données de mesure	Valeurs mesurées	CO
	Plage de mesure du gaz	0...100 ppm
Matériaux	Boîtier	ABS polycarbonate résistant à la flamme UL-94-V0 et UL-94-5VA pour utilisation en intérieur
Données de sécurité	Humidité ambiante	80 % max. humidité relative, sans condensation
	Température ambiante	-20...40°C [-4...104°F]
	Classe de protection CEI/EN	II, Isolation renforcée
	Classe de protection UL	II, Isolation renforcée
	Homologation UL	cULus according to UL2075, ULC588
	Degré de pollution	2

Accessoires

Module de communication	Description	Type
	Communication Module, CAN bus, BACnet MS/TP, 1 x SPDT, max. 1.5 A (0.4 A inductif), AC 250 V	EXT-OP-6000-A
	Communication Module, CAN bus, BACnet MS/TP, 2 x SPDT, max. 1.5 A (0.4 A inductif), AC 250 V	EXT-OP-6000-B
	Communication Module, CAN bus	EXT-OP-6000-C
	Communication Module, Ventilated Cover, CAN bus, BACnet MS/TP, 2 x SPDT, max. 1.5 A (0.4 A inductif), AC 250 V	EXT-OP-6000-BVC
Accessoires mécaniques	Description	Type
	Alarm Horn	EXT-OP-5000-AL
	Splash Guard, Wall mount	EXT-OP-6000-BT
	Splash Guard, Duct Mount	EXT-OP-6000-GN


6000-A


- 1 Down position: 2...10 V (factory setting)
Up position: 4...20 mA
- 2 End of line (EOL) jumper: CAN bus
Down position: Termination OFF (factory setting)
Up position: Termination ON (first and last unit only should have this jumper in the up position)
- 3 End of line (EOL) jumper: BACnet MS/TP
Down position: Termination OFF (factory setting)
Up position: Termination ON (first and last unit only should have this jumper in the up position)
- 4 Analogue output
- 5 Binary input to limit switch
- 6 Shield connected at the 1st unit only, at others only looped through
- 7 No connection to the ground

6000-B


- 1** End of line (EOL) jumper: CAN bus
 Down position: Termination OFF (factory setting)
 Up position: Termination ON (first and last unit only should have this jumper in the up position)
- 2** End of line (EOL) jumper: BACnet MS/TP
 Down position: Termination OFF (factory setting)
 Up position: Termination ON (first and last unit only should have this jumper in the up position)
- 3** Binary input to limit switch
- 4** Shield connected at the 1st unit only, at others only looped through
- 5** No connection to the ground


6000-C




- 1 End of line (EOL) jumper: CAN bus
Down position: Termination OFF (factory setting)
Up position: Termination ON (first and last unit only should have this jumper in the up position)
- 2 Shield connected at the 1st unit only, at others only looped through
- 3 No connection to the ground

Câblage du bus CAN


CAN bus



Raccordement RS485 BACnet MS/TP



Dimensions



Type

Poids

EXT-OP-6002-A	0.95 lb [0.43 kg]
EXT-OP-6002-B	0.95 lb [0.43 kg]
EXT-OP-6002-C	0.95 lb [0.43 kg]